

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278792

Luminaire Tested: **LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1524.5 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278792

CATALOG NUMBER: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P278792

CATALOG NUMBER: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100										
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97										
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94										
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91										
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89										
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86										
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84										
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82										
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80										
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78										
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3902294
5°	3598856
10°	2425209
15°	1195703
20°	510744
25°	200762
30°	79072
35°	34631
40°	16681
45°	8024
50°	4452
55°	2494
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278792

CATALOG NUMBER: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	615.6	40.4
10°-20°	662.9	43.5
20°-30°	191.4	12.6
30°-40°	40.4	2.7
40°-50°	10.0	0.7
50°-60°	2.9	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1469.9	96.4
0°-40°	1510.3	99.1
0°-60°	1523.1	99.9
0°-90°	1524.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1524.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7910	
5°	7267	616
15°	2341	663
25°	369	191
35°	58	40
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278792

CATALOG NUMBER: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7909.6
1°	7860.0
2°	7775.9
3°	7662.3
4°	7501.2
5°	7266.8
6°	6950.5
7°	6537.8
8°	6030.2
9°	5438.4
10°	4841.0
11°	4237.0
12°	3666.8
13°	3160.7
14°	2715.6
15°	2341.0
17.5°	1547.3
20°	972.8
22.5°	598.2
25°	368.8
27.5°	225.0
30°	138.8
32.5°	87.7
35°	57.5
37.5°	38.1
40°	25.9
42.5°	18.0
45°	11.5
47.5°	7.2
50°	5.8
52.5°	4.3
55°	2.9
57.5°	2.2
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278792

CATALOG NUMBER: LDA2B158035D010 EU2B15NFL258035 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)