

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499199

Luminaire Tested: **LDA2B159040R30D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499199  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159040R30D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1147.3 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499199

CATALOG NUMBER: LDA2B159040R30D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P499199

CATALOG NUMBER: LDA2B159040R30D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94		97	95	93		95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91		94	92	90		92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87		91	89	86		90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84		89	86	84		88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81		86	83	81		85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79		84	81	79		83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77		82	79	76		81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75		80	77	74		79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2223483
5°	2120001
10°	1719288
15°	1051003
20°	459239
25°	171801
30°	71211
35°	33306
40°	15457
45°	7535
50°	4145
55°	1548
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499199

CATALOG NUMBER: LDA2B159040R30D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	381.9	33.3
10°-20°	551.3	48.1
20°-30°	164.5	14.3
30°-40°	37.8	3.3
40°-50°	9.3	0.8
50°-60°	2.1	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.8	95.7
0°-40°	1135.6	99.0
0°-60°	1147.0	100.0
0°-90°	1147.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4507	
5°	4281	382
15°	2058	551
25°	316	165
35°	55	38
45°	11	9
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499199

CATALOG NUMBER: LDA2B159040R30D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4506.8
1°	4496.6
2°	4450.9
3°	4420.2
4°	4363.1
5°	4280.7
6°	4168.3
7°	4034.3
8°	3863.6
9°	3655.6
10°	3431.9
11°	3192.7
12°	2921.0
13°	2628.8
14°	2351.1
15°	2057.7
16°	1774.0
17°	1494.4
18°	1269.0
19°	1050.2
20°	874.7
21°	708.7
22.5°	525.4
23°	473.7
24°	387.7
25°	315.6
26°	259.1
27°	215.8
28°	177.9
29°	149.1
30°	125.0
32.5°	81.8
35°	55.3
37.5°	36.7
40°	24.0
42.5°	15.6
45°	10.8
47.5°	7.8
50°	5.4
52.5°	3.6
55°	1.8
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P499199

CATALOG NUMBER: LDA2B159040R30D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)