

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499264

Luminaire Tested: **LDA2B159040R45D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499264  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159040R45D010 2LBDL1WMH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1161.0 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499264

CATALOG NUMBER: LDA2B159040R45D010 2LBDL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P499264

CATALOG NUMBER: LDA2B159040R45D010 2LBDL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1150717
5°	1125348
10°	1044127
15°	890418
20°	670351
25°	404136
30°	194889
35°	88355
40°	40639
45°	21001
50°	11052
55°	4129
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499264

CATALOG NUMBER: LDA2B159040R45D010 2LBDL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.3	18.2
10°-20°	476.1	41.0
20°-30°	340.1	29.3
30°-40°	102.0	8.8
40°-50°	25.3	2.2
50°-60°	5.3	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1027.4	88.5
0°-40°	1129.4	97.3
0°-60°	1160.0	99.9
0°-90°	1161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1161.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2332	
5°	2272	211
15°	1743	476
25°	742	340
35°	147	102
45°	30	25
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499264

CATALOG NUMBER: LDA2B159040R45D010 2LBDL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2332.4
1°	2336.7
2°	2331.2
3°	2311.4
4°	2297.0
5°	2272.3
6°	2247.7
7°	2221.2
8°	2178.0
9°	2137.1
10°	2084.2
11°	2031.3
12°	1964.5
13°	1893.0
14°	1826.3
15°	1743.3
16°	1662.2
17°	1570.2
18°	1483.0
19°	1376.0
20°	1276.8
21°	1166.8
22.5°	1002.7
23°	947.4
24°	839.8
25°	742.4
26°	645.0
27°	556.1
28°	473.1
29°	405.2
30°	342.1
32.5°	224.8
35°	146.7
37.5°	96.2
40°	63.1
42.5°	42.7
45°	30.1
47.5°	21.6
50°	14.4
52.5°	9.0
55°	4.8
57.5°	2.4
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P499264

CATALOG NUMBER: LDA2B159040R45D010 2LBDL1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)