

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280586

Luminaire Tested: **LDA2B158035D010 EU2B15WFL558035 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1529.7 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280586

CATALOG NUMBER: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P280586

CATALOG NUMBER: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1306471
5°	1279865
10°	1190161
15°	1039153
20°	860358
25°	658028
30°	360098
35°	133285
40°	46113
45°	20792
50°	9824
55°	4903
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280586

CATALOG NUMBER: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.1	15.7
10°-20°	562.3	36.8
20°-30°	531.5	34.7
30°-40°	163.6	10.7
40°-50°	25.9	1.7
50°-60°	5.5	0.4
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1333.9	87.2
0°-40°	1497.5	97.9
0°-60°	1528.9	99.9
0°-90°	1529.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1529.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2648	
5°	2584	240
15°	2034	562
25°	1209	531
35°	221	164
45°	30	26
55°	6	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280586

CATALOG NUMBER: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2648.1
1°	2638.2
2°	2626.1
3°	2616.2
4°	2603.4
5°	2584.3
6°	2559.5
7°	2526.1
8°	2481.4
9°	2429.6
10°	2375.7
11°	2316.1
12°	2253.0
13°	2184.2
14°	2112.5
15°	2034.5
17.5°	1828.1
20°	1638.7
22.5°	1446.4
25°	1208.8
27.5°	922.2
30°	632.1
32.5°	388.0
35°	221.3
37.5°	123.4
40°	71.6
42.5°	44.7
45°	29.8
47.5°	19.9
50°	12.8
52.5°	8.5
55°	5.7
57.5°	3.5
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280586

CATALOG NUMBER: LDA2B158035D010 EU2B15WFL558035 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)