

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499277

Luminaire Tested: **LDA2B159040R60D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159040R60D010 2LBD1WMH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1186.4 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499277

CATALOG NUMBER: LDA2B159040R60D010 2LBD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P499277

CATALOG NUMBER: LDA2B159040R60D010 2LBD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	710293
5°	674327
10°	660132
15°	638968
20°	584195
25°	518670
30°	388013
35°	219051
40°	82437
45°	36909
50°	17960
55°	3613
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499277

CATALOG NUMBER: LDA2B159040R60D010 2LBD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	10.9
10°-20°	347.5	29.3
20°-30°	424.5	35.8
30°-40°	231.5	19.5
40°-50°	46.3	3.9
50°-60°	6.6	0.6
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	900.9	75.9
0°-40°	1132.4	95.4
0°-60°	1185.4	99.9
0°-90°	1186.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1186.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1440	
5°	1362	129
15°	1251	347
25°	953	425
35°	364	232
45°	53	46
55°	4	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499277

CATALOG NUMBER: LDA2B159040R60D010 2LBD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1439.7
1°	1433.1
2°	1420.5
3°	1403.7
4°	1379.6
5°	1361.6
6°	1352.0
7°	1340.6
8°	1331.5
9°	1327.3
10°	1317.7
11°	1306.9
12°	1297.3
13°	1285.8
14°	1269.0
15°	1251.0
16°	1228.1
17°	1196.3
18°	1175.8
19°	1142.8
20°	1112.7
21°	1085.1
22.5°	1038.8
23°	1019.5
24°	990.1
25°	952.8
26°	905.3
27°	855.4
28°	798.3
29°	744.2
30°	681.1
32.5°	522.4
35°	363.7
37.5°	227.8
40°	128.0
42.5°	80.0
45°	52.9
47.5°	36.1
50°	23.4
52.5°	12.0
55°	4.2
57.5°	1.8
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P499277

CATALOG NUMBER: LDA2B159040R60D010 2LBD1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)