

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499315

Luminaire Tested: **LDA2B159040R70D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499315  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159040R70D010 2LBD1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1178.8 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499315  
CATALOG NUMBER: LDA2B159040R70D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P499315

CATALOG NUMBER: LDA2B159040R70D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	460603
5°	455478
10°	453230
15°	451670
20°	435560
25°	417582
30°	413364
35°	352998
40°	220325
45°	101937
50°	36918
55°	2580
60°	1184
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499315

CATALOG NUMBER: LDA2B159040R70D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.2	7.4
10°-20°	247.7	21.0
20°-30°	356.1	30.2
30°-40°	351.0	29.8
40°-50°	125.1	10.6
50°-60°	10.3	0.9
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	691.0	58.6
0°-40°	1042.1	88.4
0°-60°	1177.4	99.9
0°-90°	1178.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1178.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	934	
5°	920	87
15°	884	248
25°	767	356
35°	586	351
45°	146	125
55°	3	10
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P499315

CATALOG NUMBER: LDA2B159040R70D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	933.6
1°	933.6
2°	931.8
3°	932.4
4°	924.6
5°	919.7
6°	913.1
7°	910.7
8°	907.7
9°	907.1
10°	904.7
11°	901.7
12°	901.7
13°	896.3
14°	889.1
15°	884.3
16°	874.7
17°	869.3
18°	852.4
19°	841.0
20°	829.6
21°	814.5
22.5°	793.5
23°	785.1
24°	777.3
25°	767.1
26°	761.0
27°	750.8
28°	749.6
29°	738.8
30°	725.6
32.5°	674.5
35°	586.1
37.5°	471.3
40°	342.1
42.5°	233.8
45°	146.1
47.5°	87.2
50°	48.1
52.5°	18.0
55°	3.0
57.5°	1.8
60°	1.2
62.5°	1.2
65°	1.2



TEST NUMBER: P499315

CATALOG NUMBER: LDA2B159040R70D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)