

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497732

Luminaire Tested: **LDA2B158035R35D010 2LBPIN1H**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158035R35D010 2LBPIN1H
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1166.3 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497732

CATALOG NUMBER: LDA2B158035R35D010 2LBPIN1H

Luminous Intensity Polar Plot





TEST NUMBER: P497732

CATALOG NUMBER: LDA2B158035R35D010 2LBPIN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98	100	98	96	97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1832888
5°	1763176
10°	1596850
15°	1111579
20°	544713
25°	203211
30°	89213
35°	43364
40°	19901
45°	10745
50°	5296
55°	1462
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P497732

CATALOG NUMBER: LDA2B158035R35D010 2LBPIN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.9	28.2
10°-20°	576.6	49.4
20°-30°	196.5	16.8
30°-40°	48.9	4.2
40°-50°	12.6	1.1
50°-60°	2.3	0.2
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.0	94.5
0°-40°	1150.9	98.7
0°-60°	1165.8	100.0
0°-90°	1166.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1166.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3715	
5°	3560	329
15°	2176	577
25°	373	196
35°	72	49
45°	15	13
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497732

CATALOG NUMBER: LDA2B158035R35D010 2LBPIN1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3715.1
1°	3707.7
2°	3679.1
3°	3651.7
4°	3607.7
5°	3560.2
6°	3513.9
7°	3470.5
8°	3376.7
9°	3285.8
10°	3187.5
11°	3026.3
12°	2851.4
13°	2626.1
14°	2417.5
15°	2176.3
16°	1940.7
17°	1695.5
18°	1466.3
19°	1234.2
20°	1037.5
21°	850.0
22.5°	623.7
23°	560.2
24°	457.3
25°	373.3
26°	308.7
27°	257.8
28°	217.2
29°	183.5
30°	156.6
32.5°	106.3
35°	72.0
37.5°	48.6
40°	30.9
42.5°	21.2
45°	15.4
47.5°	10.9
50°	6.9
52.5°	4.0
55°	1.7
57.5°	1.1
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P497732

CATALOG NUMBER: LDA2B158035R35D010 2LBPIN1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)