

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279788

Luminaire Tested: **LDA2B159035D010 EU2B15FL409035 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159035D010 EU2B15FL409035 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1299.7 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279788

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279788

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1787104
5°	1749309
10°	1594396
15°	1245553
20°	737397
25°	274142
30°	85681
35°	38064
40°	17647
45°	8303
50°	4605
55°	2580
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279788

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.5	25.1
10°-20°	649.3	50.0
20°-30°	265.9	20.5
30°-40°	44.0	3.4
40°-50°	10.4	0.8
50°-60°	2.8	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.7	95.5
0°-40°	1285.8	98.9
0°-60°	1299.0	99.9
0°-90°	1299.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3622	
5°	3532	327
15°	2439	649
25°	504	266
35°	63	44
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279788

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3622.3
1°	3609.8
2°	3593.1
3°	3578.2
4°	3558.5
5°	3532.2
6°	3493.4
7°	3442.7
8°	3370.5
9°	3282.8
10°	3182.6
11°	3066.2
12°	2935.0
13°	2785.2
14°	2618.7
15°	2438.6
17.5°	1933.8
20°	1404.5
22.5°	899.2
25°	503.6
27.5°	265.5
30°	150.4
32.5°	95.5
35°	63.2
37.5°	41.8
40°	27.4
42.5°	17.9
45°	11.9
47.5°	8.4
50°	6.0
52.5°	4.2
55°	3.0
57.5°	1.8
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279788

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)