

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278887

Luminaire Tested: **LDA2B159035D010 EU2B15NFL259035 2LBAD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278887  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl, Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1262.7 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278887

CATALOG NUMBER: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P278887

CATALOG NUMBER: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100	100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97	97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94	94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91	91	91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89	89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86	86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3231914
5°	2980591
10°	2008550
15°	990273
20°	423012
25°	166303
30°	65457
35°	28669
40°	13782
45°	6628
50°	3684
55°	2064
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278887

CATALOG NUMBER: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	509.8	40.4
10°-20°	549.0	43.5
20°-30°	158.5	12.6
30°-40°	33.5	2.6
40°-50°	8.2	0.7
50°-60°	2.4	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1217.4	96.4
0°-40°	1250.8	99.1
0°-60°	1261.5	99.9
0°-90°	1262.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1262.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6551	
5°	6018	510
15°	1939	549
25°	306	159
35°	48	33
45°	10	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278887

CATALOG NUMBER: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6550.8
1°	6509.7
2°	6440.0
3°	6345.9
4°	6212.5
5°	6018.4
6°	5756.4
7°	5414.6
8°	4994.2
9°	4504.1
10°	4009.3
11°	3509.1
12°	3036.9
13°	2617.7
14°	2249.1
15°	1938.8
17.5°	1281.4
20°	805.7
22.5°	495.4
25°	305.5
27.5°	186.4
30°	114.9
32.5°	72.6
35°	47.6
37.5°	31.6
40°	21.4
42.5°	14.9
45°	9.5
47.5°	6.0
50°	4.8
52.5°	3.6
55°	2.4
57.5°	1.8
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278887

CATALOG NUMBER: LDA2B159035D010 EU2B15NFL259035 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)