

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497754

Luminaire Tested: **LDA2B158035R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158035R45D010 2LBDLC1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1469.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497754

CATALOG NUMBER: LDA2B158035R45D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P497754

CATALOG NUMBER: LDA2B158035R45D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1456009
5°	1423883
10°	1321065
15°	1126647
20°	848177
25°	511376
30°	246560
35°	111784
40°	51459
45°	26513
50°	14046
55°	5247
60°	1480
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P497754

CATALOG NUMBER: LDA2B158035R45D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.3	18.2
10°-20°	602.3	41.0
20°-30°	430.3	29.3
30°-40°	129.0	8.8
40°-50°	32.0	2.2
50°-60°	6.7	0.5
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.0	88.5
0°-40°	1429.0	97.3
0°-60°	1467.7	99.9
0°-90°	1469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2951	
5°	2875	267
15°	2206	602
25°	939	430
35°	186	129
45°	38	32
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497754

CATALOG NUMBER: LDA2B158035R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2951.2
1°	2956.5
2°	2949.7
3°	2924.6
4°	2906.3
5°	2875.1
6°	2843.9
7°	2810.5
8°	2755.7
9°	2704.0
10°	2637.0
11°	2570.1
12°	2485.7
13°	2395.2
14°	2310.7
15°	2205.8
16°	2103.1
17°	1986.7
18°	1876.4
19°	1741.0
20°	1615.5
21°	1476.3
22.5°	1268.7
23°	1198.7
24°	1062.6
25°	939.4
26°	816.1
27°	703.6
28°	598.6
29°	512.7
30°	432.8
32.5°	284.5
35°	185.6
37.5°	121.7
40°	79.9
42.5°	54.0
45°	38.0
47.5°	27.4
50°	18.3
52.5°	11.4
55°	6.1
57.5°	3.0
60°	1.5
62.5°	1.5
65°	0.8



TEST NUMBER: P497754

CATALOG NUMBER: LDA2B158035R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)