

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499474

Luminaire Tested: **LDA2B159050R45D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499474  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159050R45D010 2LBDL1LI  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1192.7 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499474

CATALOG NUMBER: LDA2B159050R45D010 2LBDL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P499474

CATALOG NUMBER: LDA2B159050R45D010 2LBDL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1182243
5°	1156153
10°	1072683
15°	914781
20°	688727
25°	415187
30°	200187
35°	90764
40°	41734
45°	21560
50°	11360
55°	4215
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499474

CATALOG NUMBER: LDA2B159050R45D010 2LBDL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.0	18.2
10°-20°	489.1	41.0
20°-30°	349.4	29.3
30°-40°	104.7	8.8
40°-50°	26.0	2.2
50°-60°	5.4	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1055.6	88.5
0°-40°	1160.3	97.3
0°-60°	1191.7	99.9
0°-90°	1192.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1192.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2396	
5°	2334	217
15°	1791	489
25°	763	349
35°	151	105
45°	31	26
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499474

CATALOG NUMBER: LDA2B159050R45D010 2LBDL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2396.3
1°	2400.6
2°	2395.0
3°	2374.6
4°	2359.8
5°	2334.5
6°	2309.2
7°	2282.0
8°	2237.5
9°	2195.5
10°	2141.2
11°	2086.8
12°	2018.3
13°	1944.8
14°	1876.2
15°	1791.0
16°	1707.6
17°	1613.2
18°	1523.6
19°	1413.7
20°	1311.8
21°	1198.7
22.5°	1030.1
23°	973.3
24°	862.8
25°	762.7
26°	662.7
27°	571.3
28°	486.0
29°	416.3
30°	351.4
32.5°	231.0
35°	150.7
37.5°	98.8
40°	64.8
42.5°	43.8
45°	30.9
47.5°	22.2
50°	14.8
52.5°	9.3
55°	4.9
57.5°	2.5
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P499474

CATALOG NUMBER: LDA2B159050R45D010 2LBDL1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)