

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497807

Luminaire Tested: **LDA2B158035R70D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158035R70D010 2LBD1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1393.7 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497807

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P497807

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	544573
5°	538531
10°	535840
15°	534006
20°	514944
25°	493684
30°	488733
35°	417382
40°	260449
45°	120496
50°	43673
55°	3097
60°	1381
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497807

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.2	7.4
10°-20°	292.8	21.0
20°-30°	421.0	30.2
30°-40°	415.0	29.8
40°-50°	147.9	10.6
50°-60°	12.2	0.9
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.0	58.6
0°-40°	1232.0	88.4
0°-60°	1392.1	99.9
0°-90°	1393.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1104	
5°	1087	103
15°	1046	293
25°	907	421
35°	693	415
45°	173	148
55°	4	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497807

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1103.8
1°	1103.8
2°	1101.6
3°	1102.3
4°	1093.1
5°	1087.4
6°	1079.6
7°	1076.8
8°	1073.2
9°	1072.5
10°	1069.6
11°	1066.1
12°	1066.1
13°	1059.7
14°	1051.2
15°	1045.5
16°	1034.1
17°	1027.7
18°	1007.8
19°	994.3
20°	980.8
21°	963.0
22.5°	938.2
23°	928.2
24°	919.0
25°	906.9
26°	899.8
27°	887.7
28°	886.3
29°	873.5
30°	857.9
32.5°	797.4
35°	693.0
37.5°	557.2
40°	404.4
42.5°	276.5
45°	172.7
47.5°	103.1
50°	56.9
52.5°	21.3
55°	3.6
57.5°	2.1
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P497807

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)