

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499536

Luminaire Tested: **LDA2B159050R70D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159050R70D010 2LBD1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1211.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499536

CATALOG NUMBER: LDA2B159050R70D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P499536

CATALOG NUMBER: LDA2B159050R70D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	473183
5°	467958
10°	465654
15°	464031
20°	447479
25°	428959
30°	424643
35°	362695
40°	226315
45°	104728
50°	37916
55°	2666
60°	1184
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499536

CATALOG NUMBER: LDA2B159050R70D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	7.4
10°-20°	254.4	21.0
20°-30°	365.9	30.2
30°-40°	360.6	29.8
40°-50°	128.5	10.6
50°-60°	10.6	0.9
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.9	58.6
0°-40°	1070.6	88.4
0°-60°	1209.7	99.9
0°-90°	1211.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1211.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	959	
5°	945	90
15°	908	254
25°	788	366
35°	602	361
45°	150	129
55°	3	11
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P499536

CATALOG NUMBER: LDA2B159050R70D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	959.1
1°	959.1
2°	957.3
3°	957.9
4°	949.9
5°	944.9
6°	938.1
7°	935.6
8°	932.6
9°	931.9
10°	929.5
11°	926.4
12°	926.4
13°	920.8
14°	913.4
15°	908.5
16°	898.6
17°	893.0
18°	875.7
19°	864.0
20°	852.3
21°	836.8
22.5°	815.2
23°	806.6
24°	798.5
25°	788.0
26°	781.9
27°	771.4
28°	770.1
29°	759.0
30°	745.4
32.5°	692.9
35°	602.2
37.5°	484.2
40°	351.4
42.5°	240.2
45°	150.1
47.5°	89.6
50°	49.4
52.5°	18.5
55°	3.1
57.5°	1.9
60°	1.2
62.5°	1.2
65°	1.2



TEST NUMBER: P499536

CATALOG NUMBER: LDA2B159050R70D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)