

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279703

Luminaire Tested: **LDA2B158040D010 EU2B15FL408040 2LBAD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279703  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158040D010 EU2B15FL408040 2LBAD1WH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1628.7 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279703

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P279703

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																												
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2239616
5°	2192257
10°	1998079
15°	1560900
20°	924148
25°	343548
30°	107329
35°	47761
40°	22155
45°	10466
50°	5757
55°	3183
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279703

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	409.2	25.1
10°-20°	813.7	50.0
20°-30°	333.2	20.5
30°-40°	55.2	3.4
40°-50°	13.1	0.8
50°-60°	3.4	0.2
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1556.1	95.5
0°-40°	1611.3	98.9
0°-60°	1627.8	99.9
0°-90°	1628.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1628.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4540	
5°	4427	409
15°	3056	814
25°	631	333
35°	79	55
45°	15	13
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279703

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4539.5
1°	4523.8
2°	4502.8
3°	4484.1
4°	4459.5
5°	4426.6
6°	4378.0
7°	4314.4
8°	4223.9
9°	4114.0
10°	3988.4
11°	3842.6
12°	3678.1
13°	3490.4
14°	3281.8
15°	3056.0
17.5°	2423.4
20°	1760.2
22.5°	1126.8
25°	631.1
27.5°	332.7
30°	188.4
32.5°	119.6
35°	79.3
37.5°	52.3
40°	34.4
42.5°	22.4
45°	15.0
47.5°	10.5
50°	7.5
52.5°	5.2
55°	3.7
57.5°	2.2
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279703

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)