

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279834

Luminaire Tested: **LDA2B159727D010 EU2B15FL409727 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159727D010 EU2B15FL409727 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1071.4 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279834

CATALOG NUMBER: LDA2B159727D010 EU2B15FL409727 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279834

CATALOG NUMBER: LDA2B159727D010 EU2B15FL409727 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1473228
5°	1442058
10°	1314352
15°	1026741
20°	607874
25°	225966
30°	70584
35°	31379
40°	14555
45°	6838
50°	3761
55°	2150
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279834

CATALOG NUMBER: LDA2B159727D010 EU2B15FL409727 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.2	25.1
10°-20°	535.3	50.0
20°-30°	219.2	20.5
30°-40°	36.3	3.4
40°-50°	8.6	0.8
50°-60°	2.3	0.2
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.6	95.5
0°-40°	1059.9	98.9
0°-60°	1070.8	99.9
0°-90°	1071.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1071.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2986	
5°	2912	269
15°	2010	535
25°	415	219
35°	52	36
45°	10	9
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279834

CATALOG NUMBER: LDA2B159727D010 EU2B15FL409727 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2986.1
1°	2975.7
2°	2962.0
3°	2949.7
4°	2933.4
5°	2911.8
6°	2879.8
7°	2838.0
8°	2778.5
9°	2706.2
10°	2623.6
11°	2527.6
12°	2419.4
13°	2296.0
14°	2158.8
15°	2010.2
17.5°	1594.1
20°	1157.8
22.5°	741.2
25°	415.1
27.5°	218.9
30°	123.9
32.5°	78.7
35°	52.1
37.5°	34.4
40°	22.6
42.5°	14.8
45°	9.8
47.5°	6.9
50°	4.9
52.5°	3.4
55°	2.5
57.5°	1.5
60°	1.0
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279834

CATALOG NUMBER: LDA2B159727D010 EU2B15FL409727 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)