

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280609

Luminaire Tested: **LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1585.8 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280609

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280609

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76		
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72		
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62		
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1354377
5°	1326765
10°	1233796
15°	1077256
20°	891859
25°	682143
30°	373258
35°	138164
40°	47852
45°	21560
50°	10131
55°	5075
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280609

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.9	15.7
10°-20°	582.9	36.8
20°-30°	551.0	34.7
30°-40°	169.6	10.7
40°-50°	26.8	1.7
50°-60°	5.7	0.4
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1382.8	87.2
0°-40°	1552.4	97.9
0°-60°	1584.9	99.9
0°-90°	1585.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1585.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2745	
5°	2679	249
15°	2109	583
25°	1253	551
35°	229	170
45°	31	27
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280609

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2745.2
1°	2734.9
2°	2722.4
3°	2712.1
4°	2698.9
5°	2679.0
6°	2653.3
7°	2618.7
8°	2572.4
9°	2518.7
10°	2462.8
11°	2401.0
12°	2335.6
13°	2264.2
14°	2190.0
15°	2109.1
17.5°	1895.1
20°	1698.7
22.5°	1499.4
25°	1253.1
27.5°	956.0
30°	655.2
32.5°	402.3
35°	229.4
37.5°	128.0
40°	74.3
42.5°	46.3
45°	30.9
47.5°	20.6
50°	13.2
52.5°	8.8
55°	5.9
57.5°	3.7
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280609

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)