

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278942

Luminaire Tested: **LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 978.4 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278942

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P278942

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2504255
5°	2309532
10°	1556372
15°	767323
20°	327773
25°	128851
30°	50759
35°	22224
40°	10691
45°	5163
50°	2840
55°	1548
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278942

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.0	40.4
10°-20°	425.4	43.5
20°-30°	122.8	12.6
30°-40°	25.9	2.7
40°-50°	6.4	0.7
50°-60°	1.8	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	943.3	96.4
0°-40°	969.2	99.1
0°-60°	977.5	99.9
0°-90°	978.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5076	
5°	4663	395
15°	1502	425
25°	237	123
35°	37	26
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278942

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5075.9
1°	5044.1
2°	4990.1
3°	4917.2
4°	4813.9
5°	4663.4
6°	4460.4
7°	4195.6
8°	3869.8
9°	3490.1
10°	3106.7
11°	2719.1
12°	2353.2
13°	2028.3
14°	1742.7
15°	1502.3
17.5°	992.9
20°	624.3
22.5°	383.9
25°	236.7
27.5°	144.4
30°	89.1
32.5°	56.3
35°	36.9
37.5°	24.5
40°	16.6
42.5°	11.5
45°	7.4
47.5°	4.6
50°	3.7
52.5°	2.8
55°	1.8
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278942

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)