

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280729

Luminaire Tested: **LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1062.4 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280729

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280729

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72	72	72	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62	62	62	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	907292
5°	888819
10°	826555
15°	721661
20°	597478
25°	456994
30°	250035
35°	92571
40°	32073
45°	14443
50°	6831
55°	3355
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280729

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	15.7
10°-20°	390.5	36.8
20°-30°	369.1	34.7
30°-40°	113.6	10.7
40°-50°	18.0	1.7
50°-60°	3.8	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.4	87.2
0°-40°	1040.0	97.9
0°-60°	1061.8	99.9
0°-90°	1062.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1839	
5°	1795	167
15°	1413	391
25°	840	369
35°	154	114
45°	21	18
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280729

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1839.0
1°	1832.1
2°	1823.8
3°	1816.9
4°	1808.0
5°	1794.7
6°	1777.4
7°	1754.3
8°	1723.3
9°	1687.3
10°	1649.9
11°	1608.5
12°	1564.6
13°	1516.8
14°	1467.1
15°	1412.9
17.5°	1269.5
20°	1138.0
22.5°	1004.5
25°	839.5
27.5°	640.4
30°	438.9
32.5°	269.5
35°	153.7
37.5°	85.7
40°	49.8
42.5°	31.0
45°	20.7
47.5°	13.8
50°	8.9
52.5°	5.9
55°	3.9
57.5°	2.5
60°	1.0
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280729

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)