

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499707

Luminaire Tested: **LDA2B159727R60D010 2LBD1WH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159727R60D010 2LBD1WH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 965.1 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499707

CATALOG NUMBER: LDA2B159727R60D010 2LBD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P499707

CATALOG NUMBER: LDA2B159727R60D010 2LBD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	577776
5°	548535
10°	536993
15°	519755
20°	475200
25°	421937
30°	315606
35°	178155
40°	67109
45°	30002
50°	14660
55°	2925
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P499707

CATALOG NUMBER: LDA2B159727R60D010 2LBD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.9	10.9
10°-20°	282.6	29.3
20°-30°	345.3	35.8
30°-40°	188.3	19.5
40°-50°	37.7	3.9
50°-60°	5.4	0.6
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	732.8	75.9
0°-40°	921.1	95.4
0°-60°	964.2	99.9
0°-90°	965.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1171	
5°	1108	105
15°	1018	283
25°	775	345
35°	296	188
45°	43	38
55°	3	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499707

CATALOG NUMBER: LDA2B159727R60D010 2LBD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1171.1
1°	1165.8
2°	1155.5
3°	1141.8
4°	1122.2
5°	1107.6
6°	1099.7
7°	1090.5
8°	1083.1
9°	1079.7
10°	1071.9
11°	1063.1
12°	1055.2
13°	1046.0
14°	1032.3
15°	1017.6
16°	999.0
17°	973.1
18°	956.5
19°	929.6
20°	905.1
21°	882.6
22.5°	845.0
23°	829.3
24°	805.4
25°	775.1
26°	736.4
27°	695.8
28°	649.4
29°	605.4
30°	554.0
32.5°	424.9
35°	295.8
37.5°	185.3
40°	104.2
42.5°	65.0
45°	43.0
47.5°	29.3
50°	19.1
52.5°	9.8
55°	3.4
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5



TEST NUMBER: P499707

CATALOG NUMBER: LDA2B159727R60D010 2LBD1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)