

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499711

Luminaire Tested: **LDA2B159727R60D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499711  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159727R60D010 2LBDL1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 890.3 lumens  
Efficiency: N/A  
Efficacy: 63.1 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499711  
CATALOG NUMBER: LDA2B159727R60D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P499711

CATALOG NUMBER: LDA2B159727R60D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	526910
5°	513174
10°	499019
15°	474297
20°	433355
25°	372128
30°	276924
35°	162556
40°	77478
45°	36142
50°	18037
55°	6279
60°	1480
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P499711

CATALOG NUMBER: LDA2B159727R60D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.5	11.0
10°-20°	258.4	29.0
20°-30°	306.8	34.5
30°-40°	173.2	19.5
40°-50°	45.0	5.1
50°-60°	8.2	0.9
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.7	74.4
0°-40°	835.9	93.9
0°-60°	889.1	99.9
0°-90°	890.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1068	
5°	1036	98
15°	929	258
25°	684	307
35°	270	173
45°	52	45
55°	7	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499711

CATALOG NUMBER: LDA2B159727R60D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1068.0
1°	1068.5
2°	1061.1
3°	1054.8
4°	1042.5
5°	1036.2
6°	1024.9
7°	1016.6
8°	1008.8
9°	1003.4
10°	996.1
11°	981.9
12°	968.7
13°	961.4
14°	944.2
15°	928.6
16°	910.5
17°	889.0
18°	868.5
19°	844.0
20°	825.4
21°	800.0
22.5°	757.9
23°	750.6
24°	714.9
25°	683.6
26°	648.9
27°	608.8
28°	569.2
29°	530.6
30°	486.1
32.5°	374.1
35°	269.9
37.5°	184.4
40°	120.3
42.5°	78.7
45°	51.8
47.5°	35.2
50°	23.5
52.5°	14.7
55°	7.3
57.5°	2.9
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P499711

CATALOG NUMBER: LDA2B159727R60D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)