

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499757

Luminaire Tested: **LDA2B159727R70D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499757  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159727R70D010 2LBDL1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 887.9 lumens  
Efficiency: N/A  
Efficacy: 63.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499757

CATALOG NUMBER: LDA2B159727R70D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P499757

CATALOG NUMBER: LDA2B159727R70D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	351520
5°	349446
10°	347124
15°	340681
20°	328350
25°	314371
30°	299483
35°	247117
40°	160623
45°	83936
50°	39068
55°	14278
60°	1480
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P499757

CATALOG NUMBER: LDA2B159727R70D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.7	7.5
10°-20°	187.4	21.1
20°-30°	266.0	30.0
30°-40°	248.8	28.0
40°-50°	100.1	11.3
50°-60°	17.5	2.0
60°-70°	0.9	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.2	58.6
0°-40°	769.0	86.6
0°-60°	886.6	99.9
0°-90°	887.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	887.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	712	
5°	706	67
15°	667	187
25°	578	266
35°	410	249
45°	120	100
55°	17	18
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499757

CATALOG NUMBER: LDA2B159727R70D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	712.5
1°	713.4
2°	712.0
3°	709.0
4°	707.6
5°	705.6
6°	697.8
7°	700.2
8°	693.4
9°	691.9
10°	692.9
11°	686.5
12°	685.1
13°	677.3
14°	674.3
15°	667.0
16°	662.6
17°	653.8
18°	643.5
19°	637.6
20°	625.4
21°	616.1
22.5°	599.0
23°	594.6
24°	586.3
25°	577.5
26°	570.7
27°	560.9
28°	551.1
29°	539.4
30°	525.7
32.5°	477.7
35°	410.3
37.5°	330.6
40°	249.4
42.5°	178.0
45°	120.3
47.5°	79.2
50°	50.9
52.5°	31.8
55°	16.6
57.5°	5.4
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P499757

CATALOG NUMBER: LDA2B159727R70D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)