

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497970

Luminaire Tested: **LDA2B158040R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158040R45D010 2LBDLC1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1529.1 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497970

CATALOG NUMBER: LDA2B158040R45D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P497970

CATALOG NUMBER: LDA2B158040R45D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1515558
5°	1482124
10°	1375120
15°	1172718
20°	882881
25°	532280
30°	256643
35°	116361
40°	53520
45°	27630
50°	14583
55°	5419
60°	1579
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P497970

CATALOG NUMBER: LDA2B158040R45D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.2	18.2
10°-20°	627.0	41.0
20°-30°	447.9	29.3
30°-40°	134.3	8.8
40°-50°	33.3	2.2
50°-60°	7.0	0.5
60°-70°	1.1	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1353.2	88.5
0°-40°	1487.4	97.3
0°-60°	1527.7	99.9
0°-90°	1529.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1529.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3072	
5°	2993	278
15°	2296	627
25°	978	448
35°	193	134
45°	40	33
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497970

CATALOG NUMBER: LDA2B158040R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3071.9
1°	3077.4
2°	3070.3
3°	3044.2
4°	3025.2
5°	2992.7
6°	2960.2
7°	2925.4
8°	2868.4
9°	2814.6
10°	2744.9
11°	2675.2
12°	2587.3
13°	2493.1
14°	2405.3
15°	2296.0
16°	2189.1
17°	2068.0
18°	1953.2
19°	1812.3
20°	1681.6
21°	1536.7
22.5°	1320.6
23°	1247.8
24°	1106.0
25°	977.8
26°	849.5
27°	732.3
28°	623.1
29°	533.6
30°	450.5
32.5°	296.1
35°	193.2
37.5°	126.7
40°	83.1
42.5°	56.2
45°	39.6
47.5°	28.5
50°	19.0
52.5°	11.9
55°	6.3
57.5°	3.2
60°	1.6
62.5°	1.6
65°	0.8



TEST NUMBER: P497970

CATALOG NUMBER: LDA2B158040R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)