

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497973

Luminaire Tested: **LDA2B158040R60D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158040R60D010 2LBD1GPH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1460.1 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497973
CATALOG NUMBER: LDA2B158040R60D010 2LBD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P497973

CATALOG NUMBER: LDA2B158040R60D010 2LBD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	874138
5°	829835
10°	812377
15°	786324
20°	718969
25°	638322
30°	477510
35°	269582
40°	101500
45°	45422
50°	22182
55°	4473
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P497973

CATALOG NUMBER: LDA2B158040R60D010 2LBD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	10.9
10°-20°	427.6	29.3
20°-30°	522.4	35.8
30°-40°	284.9	19.5
40°-50°	57.0	3.9
50°-60°	8.2	0.6
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1108.7	75.9
0°-40°	1393.6	95.4
0°-60°	1458.8	99.9
0°-90°	1460.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1460.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1772	
5°	1676	159
15°	1540	428
25°	1173	522
35°	448	285
45°	65	57
55°	5	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497973

CATALOG NUMBER: LDA2B158040R60D010 2LBD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1771.8
1°	1763.7
2°	1748.2
3°	1727.4
4°	1697.8
5°	1675.6
6°	1663.8
7°	1649.8
8°	1638.7
9°	1633.5
10°	1621.6
11°	1608.3
12°	1596.5
13°	1582.4
14°	1561.7
15°	1539.5
16°	1511.4
17°	1472.2
18°	1447.1
19°	1406.4
20°	1369.4
21°	1335.3
22.5°	1278.4
23°	1254.7
24°	1218.5
25°	1172.6
26°	1114.1
27°	1052.7
28°	982.5
29°	915.9
30°	838.2
32.5°	642.9
35°	447.6
37.5°	280.4
40°	157.6
42.5°	98.4
45°	65.1
47.5°	44.4
50°	28.9
52.5°	14.8
55°	5.2
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7



TEST NUMBER: P497973

CATALOG NUMBER: LDA2B158040R60D010 2LBD1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)