

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315105

Luminaire Tested: **LDA2B15NFL9727D010 PIN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15NFL9727D010 PIN1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 908.5 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315105

CATALOG NUMBER: LDA2B15NFL9727D010 PIN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P315105

CATALOG NUMBER: LDA2B15NFL9727D010 PIN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 102 | 100 | 99 | 99 | 97 | | | | | | | | | 97 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 100 | 101 | 99 | 98 | 98 | 97 | 96 | 94 | | | | | | | | | 94 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 108 | 104 | 100 | 98 | 107 | 103 | 99 | 97 | 100 | 98 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | 91 | | | | | | | | | 91 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 105 | 100 | 96 | 94 | 104 | 99 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 91 | 94 | 92 | 90 | 89 | | | | | | | | | 89 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 102 | 97 | 93 | 90 | 101 | 96 | 92 | 90 | 94 | 91 | 89 | 93 | 90 | 88 | 92 | 89 | 87 | 86 | | | | | | | | | 86 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 100 | 94 | 90 | 87 | 98 | 93 | 89 | 87 | 92 | 89 | 86 | 91 | 88 | 86 | 89 | 87 | 85 | 84 | | | | | | | | | 84 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 97 | 91 | 87 | 84 | 96 | 90 | 87 | 84 | 89 | 86 | 84 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | | | | | | | | | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 95 | 88 | 85 | 82 | 94 | 88 | 84 | 82 | 87 | 84 | 81 | 86 | 83 | 81 | 85 | 83 | 81 | 80 | | | | | | | | | 80 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 92 | 86 | 82 | 80 | 92 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 84 | 81 | 79 | 78 | | | | | | | | | 78 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 90 | 84 | 80 | 78 | 90 | 84 | 80 | 78 | 83 | 80 | 77 | 82 | 79 | 77 | 82 | 79 | 77 | 76 | | | | | | | | | 76 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2325510 |
| 5° | 2144714 |
| 10° | 1445256 |
| 15° | 712569 |
| 20° | 304357 |
| 25° | 119651 |
| 30° | 47113 |
| 35° | 20658 |
| 40° | 9918 |
| 45° | 4814 |
| 50° | 2610 |
| 55° | 1462 |
| 60° | 888 |
| 65° | 467 |
| 70° | 577 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P315105

CATALOG NUMBER: LDA2B15NFL9727D010 PIN1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 366.8 | 40.4 |
| 10°-20° | 395.1 | 43.5 |
| 20°-30° | 114.1 | 12.6 |
| 30°-40° | 24.1 | 2.7 |
| 40°-50° | 5.9 | 0.7 |
| 50°-60° | 1.7 | 0.2 |
| 60°-70° | 0.6 | 0.1 |
| 70°-80° | 0.3 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 876.0 | 96.4 |
| 0°-40° | 900.1 | 99.1 |
| 0°-60° | 907.7 | 99.9 |
| 0°-90° | 908.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 908.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4714 | |
| 5° | 4331 | 367 |
| 15° | 1395 | 395 |
| 25° | 220 | 114 |
| 35° | 34 | 24 |
| 45° | 7 | 6 |
| 55° | 2 | 2 |
| 65° | 0 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P315105

CATALOG NUMBER: LDA2B15NFL9727D010 PIN1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4713.6 |
| 1° | 4684.1 |
| 2° | 4633.9 |
| 3° | 4566.2 |
| 4° | 4470.3 |
| 5° | 4330.6 |
| 6° | 4142.1 |
| 7° | 3896.1 |
| 8° | 3593.6 |
| 9° | 3241.0 |
| 10° | 2884.9 |
| 11° | 2525.0 |
| 12° | 2185.2 |
| 13° | 1883.6 |
| 14° | 1618.3 |
| 15° | 1395.1 |
| 17.5° | 922.1 |
| 20° | 579.7 |
| 22.5° | 356.5 |
| 25° | 219.8 |
| 27.5° | 134.1 |
| 30° | 82.7 |
| 32.5° | 52.3 |
| 35° | 34.3 |
| 37.5° | 22.7 |
| 40° | 15.4 |
| 42.5° | 10.7 |
| 45° | 6.9 |
| 47.5° | 4.3 |
| 50° | 3.4 |
| 52.5° | 2.6 |
| 55° | 1.7 |
| 57.5° | 1.3 |
| 60° | 0.9 |
| 62.5° | 0.9 |
| 65° | 0.4 |
| 67.5° | 0.4 |
| 70° | 0.4 |
| 72.5° | 0.4 |
| 75° | 0.0 |
| 77.5° | 0.4 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P315105
CATALOG NUMBER: LDA2B15NFL9727D010 PIN1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)