

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498038

Luminaire Tested: **LDA2B158040R70D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158040R70D010 2LBDLC1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1450.7 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498038

CATALOG NUMBER: LDA2B158040R70D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P498038

CATALOG NUMBER: LDA2B158040R70D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93					93			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85					85			
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72					72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66					66			
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61					61			
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56					56			
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52					52			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48					48			
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45					45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	574372
5°	571019
10°	567201
15°	556684
20°	536523
25°	513662
30°	489303
35°	403771
40°	262446
45°	137172
50°	63782
55°	23396
60°	2368
65°	1868
70°	1154
75°	1525
80°	0
85°	0



TEST NUMBER: P498038

CATALOG NUMBER: LDA2B158040R70D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.0	7.5
10°-20°	306.3	21.1
20°-30°	434.7	30.0
30°-40°	406.5	28.0
40°-50°	163.5	11.3
50°-60°	28.6	2.0
60°-70°	1.4	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.0	58.6
0°-40°	1256.5	86.6
0°-60°	1448.6	99.9
0°-90°	1450.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1164	
5°	1153	109
15°	1090	306
25°	944	435
35°	670	406
45°	197	163
55°	27	29
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P498038

CATALOG NUMBER: LDA2B158040R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1164.2
1°	1165.8
2°	1163.4
3°	1158.6
4°	1156.2
5°	1153.0
6°	1140.2
7°	1144.2
8°	1133.0
9°	1130.6
10°	1132.2
11°	1121.8
12°	1119.4
13°	1106.6
14°	1101.8
15°	1089.9
16°	1082.7
17°	1068.3
18°	1051.5
19°	1041.9
20°	1021.9
21°	1006.8
22.5°	978.8
23°	971.6
24°	958.0
25°	943.6
26°	932.4
27°	916.5
28°	900.5
29°	881.3
30°	858.9
32.5°	780.6
35°	670.4
37.5°	540.1
40°	407.5
42.5°	290.8
45°	196.6
47.5°	129.4
50°	83.1
52.5°	51.9
55°	27.2
57.5°	8.8
60°	2.4
62.5°	1.6
65°	1.6



TEST NUMBER: P498038

CATALOG NUMBER: LDA2B158040R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)