

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499850

Luminaire Tested: **LDA2B159730R30D010 2LBPIN1H**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159730R30D010 2LBPIN1H
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 845.4 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499850
CATALOG NUMBER: LDA2B159730R30D010 2LBPIN1H

Luminous Intensity Polar Plot





TEST NUMBER: P499850

CATALOG NUMBER: LDA2B159730R30D010 2LBPIN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1638454
5°	1562205
10°	1266910
15°	774474
20°	338378
25°	126619
30°	52468
35°	24573
40°	11399
45°	5582
50°	3070
55°	1118
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499850

CATALOG NUMBER: LDA2B159730R30D010 2LBPIN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.4	33.3
10°-20°	406.3	48.1
20°-30°	121.3	14.3
30°-40°	27.9	3.3
40°-50°	6.9	0.8
50°-60°	1.6	0.2
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.9	95.7
0°-40°	836.8	99.0
0°-60°	845.2	100.0
0°-90°	845.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3321	
5°	3154	281
15°	1516	406
25°	233	121
35°	41	28
45°	8	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499850

CATALOG NUMBER: LDA2B159730R30D010 2LBPIN1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3321.0
1°	3313.4
2°	3279.8
3°	3257.2
4°	3215.1
5°	3154.4
6°	3071.6
7°	2972.8
8°	2847.0
9°	2693.7
10°	2528.9
11°	2352.6
12°	2152.4
13°	1937.1
14°	1732.5
15°	1516.3
16°	1307.2
17°	1101.2
18°	935.1
19°	773.9
20°	644.5
21°	522.3
22.5°	387.2
23°	349.1
24°	285.7
25°	232.6
26°	190.9
27°	159.0
28°	131.1
29°	109.9
30°	92.1
32.5°	60.2
35°	40.8
37.5°	27.0
40°	17.7
42.5°	11.5
45°	8.0
47.5°	5.8
50°	4.0
52.5°	2.7
55°	1.3
57.5°	0.9
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P499850

CATALOG NUMBER: LDA2B159730R30D010 2LBPIN1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)