

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279714

Luminaire Tested: **LDA2B158050D010 EU2B15FL408050 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158050D010 EU2B15FL408050 2LBAD1H
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1619.6 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279714

CATALOG NUMBER: LDA2B158050D010 EU2B15FL408050 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P279714

CATALOG NUMBER: LDA2B158050D010 EU2B15FL408050 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20								
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2227134
5°	2180074
10°	1986958
15°	1552217
20°	919003
25°	341643
30°	106759
35°	47460
40°	22026
45°	10396
50°	5680
55°	3183
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279714

CATALOG NUMBER: LDA2B158050D010 EU2B15FL408050 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.9	25.1
10°-20°	809.2	50.0
20°-30°	331.4	20.5
30°-40°	54.9	3.4
40°-50°	13.0	0.8
50°-60°	3.4	0.2
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1547.5	95.5
0°-40°	1602.4	98.9
0°-60°	1618.8	99.9
0°-90°	1619.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1619.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4514	
5°	4402	407
15°	3039	809
25°	628	331
35°	79	55
45°	15	13
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279714

CATALOG NUMBER: LDA2B158050D010 EU2B15FL408050 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4514.2
1°	4498.6
2°	4477.8
3°	4459.2
4°	4434.7
5°	4402.0
6°	4353.6
7°	4290.4
8°	4200.4
9°	4091.1
10°	3966.2
11°	3821.2
12°	3657.6
13°	3471.0
14°	3263.5
15°	3039.0
17.5°	2409.9
20°	1750.4
22.5°	1120.6
25°	627.6
27.5°	330.9
30°	187.4
32.5°	119.0
35°	78.8
37.5°	52.1
40°	34.2
42.5°	22.3
45°	14.9
47.5°	10.4
50°	7.4
52.5°	5.2
55°	3.7
57.5°	2.2
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279714

CATALOG NUMBER: LDA2B158050D010 EU2B15FL408050 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)