

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499862

Luminaire Tested: **LDA2B159730R35D010 2LBD1MMS**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499862  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159730R35D010 2LBD1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1061.8 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499862  
CATALOG NUMBER: LDA2B159730R35D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P499862

CATALOG NUMBER: LDA2B159730R35D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96				96
2	111	107	104	101	109	106	103	100	102	100	98	100	98	96	97	95	94	93				93
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89				89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86				86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83				83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80				80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78				78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75				75
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73				73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71				71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1668698
5°	1605242
10°	1453773
15°	1011980
20°	495938
25°	184975
30°	81237
35°	39510
40°	18097
45°	9838
50°	4759
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499862

CATALOG NUMBER: LDA2B159730R35D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	299.5	28.2
10°-20°	525.0	49.4
20°-30°	178.9	16.8
30°-40°	44.5	4.2
40°-50°	11.5	1.1
50°-60°	2.1	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.3	94.5
0°-40°	1047.8	98.7
0°-60°	1061.4	100.0
0°-90°	1061.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1061.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3382	
5°	3241	299
15°	1981	525
25°	340	179
35°	66	44
45°	14	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499862

CATALOG NUMBER: LDA2B159730R35D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3382.3
1°	3375.5
2°	3349.5
3°	3324.5
4°	3284.4
5°	3241.3
6°	3199.1
7°	3159.5
8°	3074.2
9°	2991.4
10°	2901.9
11°	2755.2
12°	2595.9
13°	2390.9
14°	2200.9
15°	1981.3
16°	1766.9
17°	1543.6
18°	1334.9
19°	1123.6
20°	944.6
21°	773.9
22.5°	567.8
23°	510.0
24°	416.3
25°	339.8
26°	281.0
27°	234.7
28°	197.8
29°	167.1
30°	142.6
32.5°	96.8
35°	65.6
37.5°	44.2
40°	28.1
42.5°	19.3
45°	14.1
47.5°	9.9
50°	6.2
52.5°	3.6
55°	1.6
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P499862

CATALOG NUMBER: LDA2B159730R35D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)