

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499929

Luminaire Tested: **LDA2B159730R60D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499929  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159730R60D010 2LBDL1LI  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 947.4 lumens  
Efficiency: N/A  
Efficacy: 67.2 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499929  
CATALOG NUMBER: LDA2B159730R60D010 2LBDL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P499929

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	560755
5°	546158
10°	531081
15°	504790
20°	461234
25°	396080
30°	294698
35°	173036
40°	82437
45°	38514
50°	19188
55°	6709
60°	1579
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P499929

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.8	11.0
10°-20°	275.0	29.0
20°-30°	326.5	34.5
30°-40°	184.3	19.5
40°-50°	47.9	5.1
50°-60°	8.7	0.9
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.3	74.4
0°-40°	889.6	93.9
0°-60°	946.2	99.9
0°-90°	947.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1137	
5°	1103	104
15°	988	275
25°	728	327
35°	287	184
45°	55	48
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499929

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1136.6
1°	1137.1
2°	1129.3
3°	1122.6
4°	1109.6
5°	1102.8
6°	1090.8
7°	1082.0
8°	1073.7
9°	1067.9
10°	1060.1
11°	1045.0
12°	1031.0
13°	1023.2
14°	1005.0
15°	988.3
16°	969.0
17°	946.1
18°	924.3
19°	898.3
20°	878.5
21°	851.4
22.5°	806.7
23°	798.9
24°	760.9
25°	727.6
26°	690.6
27°	647.9
28°	605.8
29°	564.7
30°	517.3
32.5°	398.1
35°	287.3
37.5°	196.2
40°	128.0
42.5°	83.8
45°	55.2
47.5°	37.5
50°	25.0
52.5°	15.6
55°	7.8
57.5°	3.1
60°	1.6
62.5°	1.0
65°	1.0



TEST NUMBER: P499929

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)