

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280612

Luminaire Tested: **LDA2B158050D010 EU2B15WFL558050 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280612  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1614.8 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280612

CATALOG NUMBER: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P280612

CATALOG NUMBER: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1379094
5°	1350983
10°	1256339
15°	1096920
20°	908188
25°	694609
30°	380094
35°	140693
40°	48689
45°	21978
50°	10362
55°	5161
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280612

CATALOG NUMBER: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	253.5	15.7
10°-20°	593.6	36.8
20°-30°	561.0	34.7
30°-40°	172.7	10.7
40°-50°	27.3	1.7
50°-60°	5.8	0.4
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1408.1	87.2
0°-40°	1580.8	97.9
0°-60°	1613.9	99.9
0°-90°	1614.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1614.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2795	
5°	2728	253
15°	2148	594
25°	1276	561
35°	234	173
45°	32	27
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280612

CATALOG NUMBER: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2795.3
1°	2784.8
2°	2772.1
3°	2761.6
4°	2748.1
5°	2727.9
6°	2701.7
7°	2666.5
8°	2619.4
9°	2564.7
10°	2507.8
11°	2444.9
12°	2378.2
13°	2305.6
14°	2230.0
15°	2147.6
17.5°	1929.7
20°	1729.8
22.5°	1526.8
25°	1276.0
27.5°	973.5
30°	667.2
32.5°	409.6
35°	233.6
37.5°	130.3
40°	75.6
42.5°	47.2
45°	31.5
47.5°	21.0
50°	13.5
52.5°	9.0
55°	6.0
57.5°	3.7
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280612

CATALOG NUMBER: LDA2B158050D010 EU2B15WFL558050 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)