

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499931

Luminaire Tested: **LDA2B159730R60D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499931
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159730R60D010 2LBDL1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 947.4 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499931

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P499931

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560755
5°	546158
10°	531081
15°	504790
20°	461234
25°	396080
30°	294698
35°	173036
40°	82437
45°	38514
50°	19188
55°	6709
60°	1579
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P499931

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.8	11.0
10°-20°	275.0	29.0
20°-30°	326.5	34.5
30°-40°	184.3	19.5
40°-50°	47.9	5.1
50°-60°	8.7	0.9
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.3	74.4
0°-40°	889.6	93.9
0°-60°	946.2	99.9
0°-90°	947.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1137	
5°	1103	104
15°	988	275
25°	728	327
35°	287	184
45°	55	48
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499931

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1136.6
1°	1137.1
2°	1129.3
3°	1122.6
4°	1109.6
5°	1102.8
6°	1090.8
7°	1082.0
8°	1073.7
9°	1067.9
10°	1060.1
11°	1045.0
12°	1031.0
13°	1023.2
14°	1005.0
15°	988.3
16°	969.0
17°	946.1
18°	924.3
19°	898.3
20°	878.5
21°	851.4
22.5°	806.7
23°	798.9
24°	760.9
25°	727.6
26°	690.6
27°	647.9
28°	605.8
29°	564.7
30°	517.3
32.5°	398.1
35°	287.3
37.5°	196.2
40°	128.0
42.5°	83.8
45°	55.2
47.5°	37.5
50°	25.0
52.5°	15.6
55°	7.8
57.5°	3.1
60°	1.6
62.5°	1.0
65°	1.0



TEST NUMBER: P499931

CATALOG NUMBER: LDA2B159730R60D010 2LBDL1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)