

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499951

Luminaire Tested: **LDA2B159730R65D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159730R65D010 2LBDL1H
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 974.1 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499951

CATALOG NUMBER: LDA2B159730R65D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P499951

CATALOG NUMBER: LDA2B159730R65D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	509692
5°	488412
10°	465103
15°	442068
20°	411199
25°	379640
30°	329392
35°	236336
40°	128357
45°	54841
50°	23563
55°	8515
60°	1579
65°	1167
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P499951

CATALOG NUMBER: LDA2B159730R65D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.3	9.5
10°-20°	242.4	24.9
20°-30°	317.0	32.5
30°-40°	241.1	24.8
40°-50°	69.7	7.2
50°-60°	10.5	1.1
60°-70°	0.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.7	66.9
0°-40°	892.9	91.7
0°-60°	973.1	99.9
0°-90°	974.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1033	
5°	986	92
15°	866	242
25°	697	317
35°	392	241
45°	79	70
55°	10	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499951

CATALOG NUMBER: LDA2B159730R65D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1033.1
1°	1029.4
2°	1023.7
3°	1012.2
4°	999.7
5°	986.2
6°	973.2
7°	961.8
8°	950.8
9°	940.9
10°	928.4
11°	917.5
12°	906.1
13°	894.6
14°	882.1
15°	865.5
16°	853.0
17°	837.9
18°	815.0
19°	803.0
20°	783.2
21°	765.6
22.5°	738.5
23°	728.1
24°	712.0
25°	697.4
26°	678.1
27°	656.8
28°	633.4
29°	608.4
30°	578.2
32.5°	495.5
35°	392.4
37.5°	289.4
40°	199.3
42.5°	126.5
45°	78.6
47.5°	48.9
50°	30.7
52.5°	18.2
55°	9.9
57.5°	3.6
60°	1.6
62.5°	1.0
65°	1.0



TEST NUMBER: P499951

CATALOG NUMBER: LDA2B159730R65D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)