

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499960

Luminaire Tested: **LDA2B159730R65D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499960  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159730R65D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1053.8 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499960

CATALOG NUMBER: LDA2B159730R65D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P499960

CATALOG NUMBER: LDA2B159730R65D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	551332
5°	528329
10°	503127
15°	478179
20°	444853
25°	410669
30°	356338
35°	255669
40°	138855
45°	59306
50°	25482
55°	9204
60°	1677
65°	1284
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499960

CATALOG NUMBER: LDA2B159730R65D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.9	9.5
10°-20°	262.2	24.9
20°-30°	342.9	32.5
30°-40°	260.9	24.8
40°-50°	75.4	7.2
50°-60°	11.3	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.0	66.9
0°-40°	965.9	91.7
0°-60°	1052.6	99.9
0°-90°	1053.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1053.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1118	
5°	1067	100
15°	936	262
25°	754	343
35°	424	261
45°	85	75
55°	11	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499960

CATALOG NUMBER: LDA2B159730R65D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1117.5
1°	1113.6
2°	1107.4
3°	1095.0
4°	1081.5
5°	1066.8
6°	1052.8
7°	1040.4
8°	1028.6
9°	1017.9
10°	1004.3
11°	992.5
12°	980.1
13°	967.8
14°	954.2
15°	936.2
16°	922.7
17°	906.4
18°	881.6
19°	868.7
20°	847.3
21°	828.1
22.5°	798.9
23°	787.6
24°	770.2
25°	754.4
26°	733.6
27°	710.5
28°	685.1
29°	658.1
30°	625.5
32.5°	536.0
35°	424.5
37.5°	313.0
40°	215.6
42.5°	136.8
45°	85.0
47.5°	52.9
50°	33.2
52.5°	19.7
55°	10.7
57.5°	3.9
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P499960

CATALOG NUMBER: LDA2B159730R65D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)