

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498196

Luminaire Tested: **LDA2B158050R60D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158050R60D010 2LBD1WHH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1450.6 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498196

CATALOG NUMBER: LDA2B158050R60D010 2LBD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P498196

CATALOG NUMBER: LDA2B158050R60D010 2LBD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	868465
5°	824437
10°	807117
15°	781216
20°	714244
25°	634130
30°	474377
35°	267835
40°	100856
45°	45142
50°	22028
55°	4387
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P498196

CATALOG NUMBER: LDA2B158050R60D010 2LBD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	10.9
10°-20°	424.8	29.3
20°-30°	519.0	35.8
30°-40°	283.1	19.5
40°-50°	56.7	3.9
50°-60°	8.1	0.6
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1101.4	75.9
0°-40°	1384.5	95.4
0°-60°	1449.3	99.9
0°-90°	1450.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1760	
5°	1665	158
15°	1530	425
25°	1165	519
35°	445	283
45°	65	57
55°	5	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498196

CATALOG NUMBER: LDA2B158050R60D010 2LBD1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1760.3
1°	1752.2
2°	1736.8
3°	1716.2
4°	1686.8
5°	1664.7
6°	1653.0
7°	1639.0
8°	1628.0
9°	1622.8
10°	1611.1
11°	1597.8
12°	1586.1
13°	1572.1
14°	1551.5
15°	1529.5
16°	1501.6
17°	1462.6
18°	1437.6
19°	1397.2
20°	1360.4
21°	1326.6
22.5°	1270.0
23°	1246.5
24°	1210.5
25°	1164.9
26°	1106.9
27°	1045.9
28°	976.1
29°	909.9
30°	832.7
32.5°	638.7
35°	444.7
37.5°	278.6
40°	156.6
42.5°	97.8
45°	64.7
47.5°	44.1
50°	28.7
52.5°	14.7
55°	5.1
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7



TEST NUMBER: P498196

CATALOG NUMBER: LDA2B158050R60D010 2LBD1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)