

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499973

Luminaire Tested: **LDA2B159730R70D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159730R70D010 2LBDL1GPH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 944.8 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499973
CATALOG NUMBER: LDA2B159730R70D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P499973

CATALOG NUMBER: LDA2B159730R70D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	374116
5°	371930
10°	369467
15°	362593
20°	349456
25°	334566
30°	318739
35°	262957
40°	170928
45°	89308
50°	41524
55°	15225
60°	1579
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P499973

CATALOG NUMBER: LDA2B159730R70D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.0	7.5
10°-20°	199.5	21.1
20°-30°	283.1	30.0
30°-40°	264.8	28.0
40°-50°	106.5	11.3
50°-60°	18.6	2.0
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.6	58.6
0°-40°	818.4	86.6
0°-60°	943.5	99.9
0°-90°	944.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	758	
5°	751	71
15°	710	199
25°	615	283
35°	437	265
45°	128	106
55°	18	19
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499973

CATALOG NUMBER: LDA2B159730R70D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	758.3
1°	759.3
2°	757.7
3°	754.6
4°	753.1
5°	751.0
6°	742.7
7°	745.3
8°	738.0
9°	736.4
10°	737.5
11°	730.7
12°	729.1
13°	720.8
14°	717.7
15°	709.9
16°	705.2
17°	695.8
18°	684.9
19°	678.6
20°	665.6
21°	655.7
22.5°	637.5
23°	632.8
24°	624.0
25°	614.6
26°	607.3
27°	596.9
28°	586.5
29°	574.0
30°	559.5
32.5°	508.5
35°	436.6
37.5°	351.8
40°	265.4
42.5°	189.4
45°	128.0
47.5°	84.3
50°	54.1
52.5°	33.8
55°	17.7
57.5°	5.7
60°	1.6
62.5°	1.0
65°	1.0



TEST NUMBER: P499973

CATALOG NUMBER: LDA2B159730R70D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)