

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315113

Luminaire Tested: **LDA2B15NFL9730D010 PIN1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B15NFL9730D010 PIN1MMS  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in Adj PinHole, Black oculus, matte metallic silver finish  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 967.0 lumens  
Efficiency: N/A  
Efficacy: 68.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315113  
CATALOG NUMBER: LDA2B15NFL9730D010 PIN1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P315113

CATALOG NUMBER: LDA2B15NFL9730D010 PIN1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2475048
5°	2282590
10°	1538187
15°	758385
20°	323940
25°	127327
30°	50132
35°	21983
40°	10562
45°	5093
50°	2763
55°	1548
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P315113

CATALOG NUMBER: LDA2B15NFL9730D010 PIN1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	390.4	40.4
10°-20°	420.5	43.5
20°-30°	121.4	12.6
30°-40°	25.6	2.7
40°-50°	6.3	0.7
50°-60°	1.8	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.3	96.4
0°-40°	957.9	99.1
0°-60°	966.0	99.9
0°-90°	967.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	967.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5017	
5°	4609	390
15°	1485	420
25°	234	121
35°	36	26
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315113

CATALOG NUMBER: LDA2B15NFL9730D010 PIN1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5016.7
1°	4985.2
2°	4931.9
3°	4859.8
4°	4757.7
5°	4609.0
6°	4408.4
7°	4146.6
8°	3824.6
9°	3449.3
10°	3070.4
11°	2687.3
12°	2325.7
13°	2004.7
14°	1722.4
15°	1484.8
17.5°	981.4
20°	617.0
22.5°	379.4
25°	233.9
27.5°	142.7
30°	88.0
32.5°	55.6
35°	36.5
37.5°	24.2
40°	16.4
42.5°	11.4
45°	7.3
47.5°	4.6
50°	3.6
52.5°	2.7
55°	1.8
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P315113

CATALOG NUMBER: LDA2B15NFL9730D010 PIN1MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)