

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315112

Luminaire Tested: **LDA2B15NFL9730D010 PINW1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315112  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B15NFL9730D010 PINW1MW  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in Adj PinHole, Black oculus, matte white finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 977.5 lumens  
Efficiency: N/A  
Efficacy: 69.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315112

CATALOG NUMBER: LDA2B15NFL9730D010 PINW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P315112

CATALOG NUMBER: LDA2B15NFL9730D010 PINW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2501838
5°	2307303
10°	1554819
15°	766608
20°	327458
25°	128742
30°	50702
35°	22224
40°	10691
45°	5163
50°	2840
55°	1548
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P315112

CATALOG NUMBER: LDA2B15NFL9730D010 PINW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	394.6	40.4
10°-20°	425.0	43.5
20°-30°	122.7	12.6
30°-40°	25.9	2.6
40°-50°	6.4	0.7
50°-60°	1.8	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.4	96.4
0°-40°	968.3	99.1
0°-60°	976.5	99.9
0°-90°	977.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5071	
5°	4659	395
15°	1501	425
25°	236	123
35°	37	26
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315112

CATALOG NUMBER: LDA2B15NFL9730D010 PINW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5071.0
1°	5039.2
2°	4985.3
3°	4912.5
4°	4809.2
5°	4658.9
6°	4456.1
7°	4191.5
8°	3866.1
9°	3486.7
10°	3103.6
11°	2716.4
12°	2350.9
13°	2026.4
14°	1741.0
15°	1500.9
17.5°	992.0
20°	623.7
22.5°	383.5
25°	236.5
27.5°	144.3
30°	89.0
32.5°	56.2
35°	36.9
37.5°	24.4
40°	16.6
42.5°	11.5
45°	7.4
47.5°	4.6
50°	3.7
52.5°	2.8
55°	1.8
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P315112

CATALOG NUMBER: LDA2B15NFL9730D010 PINW1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)