

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280774

Luminaire Tested: **LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2108.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280774

CATALOG NUMBER: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P280774

CATALOG NUMBER: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	97	93	91	91	90	90	90	90	90	90	95																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	90	90	90	90	90	90	90	90	90	90	90	90																
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	85	85	85	85	85	85	85	85	85	85	85																
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80	80	80	80	80	80	80	80	80	80																
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76	76	76	76	76	76	76	76	76	76																
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72	72	72	72	72	72	72	72	72	72	72	72	72																
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	68	68	68	68	68	68	68	68	68	68	68	68	68	68															
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65	65	65	65	65	65	65	65	65	65	65															
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62	62	62	62	62	62	62	62	62	62	62	62	62	62															
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59	59	59	59	59	59	59	59	59	59	59	59	59	59															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1800277
5°	1763572
10°	1639984
15°	1431881
20°	1185506
25°	906694
30°	496139
35°	183696
40°	63567
45°	28676
50°	13509
55°	6709
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P280774

CATALOG NUMBER: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.9	15.7
10°-20°	774.8	36.8
20°-30°	732.4	34.7
30°-40°	225.5	10.7
40°-50°	35.6	1.7
50°-60°	7.5	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1838.1	87.2
0°-40°	2063.5	97.9
0°-60°	2106.7	99.9
0°-90°	2108.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2108.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3649	
5°	3561	331
15°	2803	775
25°	1666	732
35°	305	225
45°	41	36
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280774

CATALOG NUMBER: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3649.0
1°	3635.3
2°	3618.7
3°	3605.0
4°	3587.4
5°	3561.0
6°	3526.8
7°	3480.8
8°	3419.3
9°	3347.9
10°	3273.6
11°	3191.5
12°	3104.5
13°	3009.7
14°	2911.0
15°	2803.4
17.5°	2519.0
20°	2258.0
22.5°	1993.1
25°	1665.6
27.5°	1270.7
30°	870.9
32.5°	534.7
35°	305.0
37.5°	170.1
40°	98.7
42.5°	61.6
45°	41.1
47.5°	27.4
50°	17.6
52.5°	11.7
55°	7.8
57.5°	4.9
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280774

CATALOG NUMBER: LDA2B208027D010 EU2B20WFL558027 2LBAD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)