

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498358

Luminaire Tested: **LDA2B159024R35D010 2LBD1WMH**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498358  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159024R35D010 2LBD1WMH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1029.1 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498358

CATALOG NUMBER: LDA2B159024R35D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P498358

CATALOG NUMBER: LDA2B159024R35D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98	100	98	96	97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1617191
5°	1555717
10°	1408936
15°	980772
20°	480608
25°	179314
30°	78730
35°	38305
40°	17518
45°	9489
50°	4682
55°	1290
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P498358

CATALOG NUMBER: LDA2B159024R35D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.2	28.2
10°-20°	508.8	49.4
20°-30°	173.4	16.8
30°-40°	43.1	4.2
40°-50°	11.1	1.1
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.4	94.5
0°-40°	1015.5	98.7
0°-60°	1028.7	100.0
0°-90°	1029.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1029.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3278	
5°	3141	290
15°	1920	509
25°	329	173
35°	64	43
45°	14	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498358

CATALOG NUMBER: LDA2B159024R35D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3277.9
1°	3271.4
2°	3246.2
3°	3222.0
4°	3183.1
5°	3141.3
6°	3100.4
7°	3062.1
8°	2979.4
9°	2899.2
10°	2812.4
11°	2670.2
12°	2515.8
13°	2317.1
14°	2133.0
15°	1920.2
16°	1712.4
17°	1496.0
18°	1293.7
19°	1088.9
20°	915.4
21°	750.0
22.5°	550.3
23°	494.3
24°	403.5
25°	329.4
26°	272.4
27°	227.5
28°	191.7
29°	161.9
30°	138.2
32.5°	93.8
35°	63.6
37.5°	42.9
40°	27.2
42.5°	18.7
45°	13.6
47.5°	9.6
50°	6.1
52.5°	3.5
55°	1.5
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P498358

CATALOG NUMBER: LDA2B159024R35D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)