

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500041

Luminaire Tested: **LDA2B208027R30D010 2LBD1WH**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208027R30D010 2LBD1WH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1831.2 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500041

CATALOG NUMBER: LDA2B208027R30D010 2LBD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P500041

CATALOG NUMBER: LDA2B208027R30D010 2LBD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	95	93	92	
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90	95	93	90	
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87	92	90	87	
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85	90	88	85	
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	88	85	82	
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80	85	83	80	
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77	83	81	77	
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75	81	78	75	
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73	79	76	73	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3548653
5°	3383573
10°	2744028
15°	1677406
20°	732934
25°	274196
30°	113709
35°	53182
40°	24731
45°	12071
50°	6601
55°	2494
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P500041

CATALOG NUMBER: LDA2B208027R30D010 2LBD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.5	33.3
10°-20°	879.9	48.1
20°-30°	262.6	14.3
30°-40°	60.3	3.3
40°-50°	14.8	0.8
50°-60°	3.4	0.2
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1752.0	95.7
0°-40°	1812.4	99.0
0°-60°	1830.6	100.0
0°-90°	1831.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7193	
5°	6832	609
15°	3284	880
25°	504	263
35°	88	60
45°	17	15
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500041

CATALOG NUMBER: LDA2B208027R30D010 2LBD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7192.8
1°	7176.5
2°	7103.6
3°	7054.7
4°	6963.5
5°	6832.1
6°	6652.7
7°	6438.7
8°	6166.3
9°	5834.3
10°	5477.4
11°	5095.5
12°	4661.9
13°	4195.6
14°	3752.3
15°	3284.1
16°	2831.3
17°	2385.1
18°	2025.4
19°	1676.1
20°	1396.0
21°	1131.2
22.5°	838.5
23°	756.0
24°	618.8
25°	503.7
26°	413.5
27°	344.4
28°	284.0
29°	237.9
30°	199.6
32.5°	130.5
35°	88.3
37.5°	58.5
40°	38.4
42.5°	24.9
45°	17.3
47.5°	12.5
50°	8.6
52.5°	5.8
55°	2.9
57.5°	1.9
60°	1.0
62.5°	1.0
65°	1.0



TEST NUMBER: P500041

CATALOG NUMBER: LDA2B208027R30D010 2LBD1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)