

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500131

Luminaire Tested: **LDA2B208027R45D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208027R45D010 2LBDLC1MW  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1983.0 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500131

CATALOG NUMBER: LDA2B208027R45D010 2LBDLC1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P500131

CATALOG NUMBER: LDA2B208027R45D010 2LBDLC1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1965504
5°	1922150
10°	1783363
15°	1520856
20°	1144974
25°	690309
30°	332810
35°	150872
40°	69427
45°	35793
50°	18881
55°	7053
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500131

CATALOG NUMBER: LDA2B208027R45D010 2LBDLC1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	360.9	18.2
10°-20°	813.1	41.0
20°-30°	580.9	29.3
30°-40°	174.1	8.8
40°-50°	43.2	2.2
50°-60°	9.0	0.5
60°-70°	1.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.9	88.5
0°-40°	1929.0	97.3
0°-60°	1981.2	99.9
0°-90°	1983.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1983.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3984	
5°	3881	361
15°	2978	813
25°	1268	581
35°	250	174
45°	51	43
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500131

CATALOG NUMBER: LDA2B208027R45D010 2LBDLC1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3983.9
1°	3991.0
2°	3981.8
3°	3947.9
4°	3923.3
5°	3881.2
6°	3839.1
7°	3793.9
8°	3720.0
9°	3650.2
10°	3559.8
11°	3469.4
12°	3355.5
13°	3233.3
14°	3119.3
15°	2977.6
16°	2839.0
17°	2681.9
18°	2533.0
19°	2350.3
20°	2180.8
21°	1993.0
22.5°	1712.6
23°	1618.2
24°	1434.4
25°	1268.1
26°	1101.7
27°	949.8
28°	808.1
29°	692.0
30°	584.2
32.5°	384.0
35°	250.5
37.5°	164.3
40°	107.8
42.5°	72.9
45°	51.3
47.5°	37.0
50°	24.6
52.5°	15.4
55°	8.2
57.5°	4.1
60°	2.1
62.5°	2.1
65°	1.0



TEST NUMBER: P500131

CATALOG NUMBER: LDA2B208027R45D010 2LBDLC1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)