

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500154

Luminaire Tested: **LDA2B208027R60D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208027R60D010 2LBDLC1MW
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1893.5 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500154

CATALOG NUMBER: LDA2B208027R60D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P500154

CATALOG NUMBER: LDA2B208027R60D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1120721
5°	1091523
10°	1061411
15°	1008813
20°	921786
25°	791560
30°	588997
35°	345771
40°	164809
45°	76958
50°	38300
55°	13418
60°	3059
65°	2452
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500154

CATALOG NUMBER: LDA2B208027R60D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.4	11.0
10°-20°	549.6	29.0
20°-30°	652.6	34.5
30°-40°	368.3	19.5
40°-50°	95.8	5.1
50°-60°	17.4	0.9
60°-70°	1.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.5	74.4
0°-40°	1777.9	93.9
0°-60°	1891.1	99.9
0°-90°	1893.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1893.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2272	
5°	2204	207
15°	1975	550
25°	1454	653
35°	574	368
45°	110	96
55°	16	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500154

CATALOG NUMBER: LDA2B208027R60D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2271.6
1°	2272.6
2°	2257.0
3°	2243.5
4°	2217.5
5°	2204.0
6°	2180.0
7°	2162.4
8°	2145.7
9°	2134.3
10°	2118.7
11°	2088.5
12°	2060.4
13°	2044.8
14°	2008.4
15°	1975.1
16°	1936.7
17°	1890.9
18°	1847.2
19°	1795.2
20°	1755.7
21°	1701.6
22.5°	1612.1
23°	1596.5
24°	1520.6
25°	1454.1
26°	1380.2
27°	1294.9
28°	1210.7
29°	1128.5
30°	1033.9
32.5°	795.7
35°	574.1
37.5°	392.1
40°	255.9
42.5°	167.5
45°	110.3
47.5°	74.9
50°	49.9
52.5°	31.2
55°	15.6
57.5°	6.2
60°	3.1
62.5°	2.1
65°	2.1



TEST NUMBER: P500154

CATALOG NUMBER: LDA2B208027R60D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)