

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500196

Luminaire Tested: **LDA2B208027R70D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208027R70D010 2LBDL1WHH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1742.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500196

CATALOG NUMBER: LDA2B208027R70D010 2LBDL1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P500196

CATALOG NUMBER: LDA2B208027R70D010 2LBDL1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	689670
5°	685669
10°	681072
15°	668439
20°	644258
25°	616819
30°	587573
35°	484838
40°	315128
45°	164662
50°	76600
55°	28041
60°	2861
65°	2218
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500196

CATALOG NUMBER: LDA2B208027R70D010 2LBDL1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.9	7.5
10°-20°	367.8	21.1
20°-30°	522.0	30.0
30°-40°	488.1	28.0
40°-50°	196.3	11.3
50°-60°	34.3	2.0
60°-70°	1.7	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1020.7	58.6
0°-40°	1508.8	86.6
0°-60°	1739.4	99.9
0°-90°	1742.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1742.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1398	
5°	1384	131
15°	1309	368
25°	1133	522
35°	805	488
45°	236	196
55°	33	34
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500196

CATALOG NUMBER: LDA2B208027R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1397.9
1°	1399.8
2°	1396.9
3°	1391.2
4°	1388.3
5°	1384.5
6°	1369.1
7°	1373.9
8°	1360.5
9°	1357.6
10°	1359.5
11°	1347.0
12°	1344.2
13°	1328.8
14°	1323.1
15°	1308.7
16°	1300.0
17°	1282.8
18°	1262.6
19°	1251.1
20°	1227.1
21°	1208.9
22.5°	1175.3
23°	1166.7
24°	1150.4
25°	1133.1
26°	1119.7
27°	1100.5
28°	1081.3
29°	1058.3
30°	1031.4
32.5°	937.4
35°	805.0
37.5°	648.6
40°	489.3
42.5°	349.2
45°	236.0
47.5°	155.4
50°	99.8
52.5°	62.4
55°	32.6
57.5°	10.6
60°	2.9
62.5°	1.9
65°	1.9



TEST NUMBER: P500196

CATALOG NUMBER: LDA2B208027R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)