

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498536

Luminaire Tested: **LDA2B159027R30D010 2LBDC1MW-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-15)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159027R30D010 2LBDC1MW-30DEG TILT
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 749.6 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 3.2 / 0.53 / 1.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498536

CATALOG NUMBER: LDA2B159027R30D010 2LBDC1MW-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P498536

CATALOG NUMBER: LDA2B159027R30D010 2LBDC1MW-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90					90			
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80					80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71					71			
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63					63			
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56					56			
6	77	66	58	52	76	65	58	52	63	57	52	62	56	51	60	55	51	49					49			
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44					44			
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8288	8288	8288
5°	18027	7528	5398
10°	54155	6513	3557
15°	328678	4699	2758
20°	1176685	2573	1155
25°	1912298	871	0
30°	2098777	285	0
35°	1907251	0	0
40°	1637016	0	0
45°	1213403	0	0
50°	820495	0	0
55°	277226	430	0
60°	39666	1085	0
65°	3152	1284	0
70°	0	1587	0
75°	0	3050	0
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P498536

CATALOG NUMBER: LDA2B159027R30D010 2LBDC1MW-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.2	0.3
10°-20°	38.6	5.2
20°-30°	219.2	29.2
30°-40°	285.6	38.1
40°-50°	167.3	22.3
50°-60°	33.8	4.5
60°-70°	1.3	0.2
70°-80°	0.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.0	34.7
0°-40°	545.6	72.8
0°-60°	746.7	99.6
0°-90°	749.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	749.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	36	26	15	12	11	6
15°	644	73	9	6	5	272
25°	3513	123	2	1	0	1554
35°	3167	90	0	0	0	1972
45°	1739	22	0	0	0	1358
55°	322	2	0	0	0	376
65°	3	0	1	1	0	8
75°	0	1	2	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P498536

CATALOG NUMBER: LDA2B159027R30D010 2LBDC1MW-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8
2.5°	22.8	21.2	20.1	17.4	15.8	14.7	14.1	13.6	13.0
5°	36.4	33.7	26.1	19.0	15.2	13.0	12.0	10.9	10.9
7.5°	62.5	50.5	34.2	20.1	14.1	11.4	10.3	8.7	8.2
10°	108.1	84.2	46.7	21.2	13.0	10.3	8.2	7.6	7.1
12.5°	253.8	153.8	59.2	21.2	11.4	8.7	7.1	6.5	6.0
15°	643.5	313.6	73.4	20.1	9.2	6.5	6.0	5.4	5.4
17.5°	1334.7	644.0	89.1	18.5	7.6	4.9	4.3	3.8	3.8
20°	2241.2	1154.3	104.3	15.8	4.9	3.3	2.7	2.2	2.2
21°	2574.9	1339.6	112.0	14.7	4.3	2.7	2.2	2.2	1.6
22°	2874.9	1509.7	116.3	14.1	3.3	2.2	2.2	1.6	1.6
23°	3068.4	1725.5	120.1	12.5	2.7	1.6	1.6	1.1	0.5
24°	3360.2	1894.5	121.7	11.4	2.2	1.6	1.1	0.5	0.5
25°	3512.9	2047.8	123.4	10.3	1.6	1.6	1.1	0.5	0.0
26°	3622.7	2169.0	129.3	9.8	1.6	1.1	1.1	0.5	0.0
27°	3708.6	2246.1	132.6	8.7	1.1	1.1	1.1	0.0	0.0
28°	3703.7	2302.1	129.9	7.6	1.1	1.1	0.5	0.0	0.0
29°	3727.1	2340.1	128.3	6.5	0.5	0.5	0.5	0.0	0.0
30°	3684.1	2343.4	122.3	6.0	0.5	0.5	0.5	0.0	0.0
31°	3618.9	2303.7	120.1	5.4	0.0	0.5	0.5	0.0	0.0
32°	3557.5	2285.8	113.0	4.3	0.0	0.5	0.5	0.0	0.0
33°	3452.1	2205.4	106.0	3.8	0.0	0.5	0.0	0.0	0.0
34°	3310.8	2126.6	99.5	3.3	0.0	0.5	0.0	0.0	0.0
35°	3166.7	2061.3	90.2	3.3	0.0	0.5	0.0	0.0	0.0
36°	3047.2	1942.9	83.7	2.7	0.0	0.5	0.0	0.0	0.0
37°	2902.1	1841.2	75.0	2.2	0.0	0.0	0.0	0.0	0.0
38°	2803.2	1698.3	68.5	2.2	0.0	0.0	0.0	0.0	0.0
39°	2670.0	1577.7	60.3	1.6	0.0	0.0	0.0	0.0	0.0
40°	2541.8	1452.7	52.2	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	2173.8	1120.6	35.9	0.5	0.0	0.0	0.0	0.0	0.0
45°	1739.1	821.7	22.3	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	1380.9	554.9	14.1	0.0	0.0	0.0	0.0	0.0	0.0
50°	1069.0	285.9	8.2	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	710.8	121.2	4.9	0.0	0.0	0.5	0.0	0.0	0.0
55°	322.3	63.0	2.2	0.0	0.5	0.5	0.5	0.0	0.0
57.5°	129.9	27.2	1.1	0.5	0.5	0.5	0.5	0.0	0.0
60°	40.2	7.6	0.5	0.5	1.1	1.1	0.5	0.0	0.0
62.5°	8.2	1.6	0.5	1.1	1.1	1.1	0.5	0.0	0.0
65°	2.7	0.5	0.5	1.1	1.1	1.1	1.1	0.0	0.0
67.5°	0.5	0.5	0.5	1.1	1.1	1.1	1.1	0.5	0.0
70°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.0
72.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
75°	0.0	0.5	1.1	1.1	1.6	1.6	1.1	0.5	0.0
77.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
80°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0



TEST NUMBER: P498536

CATALOG NUMBER: LDA2B159027R30D010 2LBDC1MW-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
85°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.0	0.0
87.5°	0.0	0.5	1.1	1.1	1.1	1.1	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)