

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279891

Luminaire Tested: **LDA2B208030D010 EU2B20FL408030 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208030D010 EU2B20FL408030 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2171.8 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279891

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279891

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|----|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 103 | 98 | 93 | 90 | 102 | 97 | 93 | 90 | 95 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 100 | 94 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 88 | 85 | 90 | 87 | 84 | 88 | 86 | 83 | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 82 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 94 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 81 | 78 | 83 | 80 | 78 | 77 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | 72 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 85 | 78 | 74 | 71 | 84 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2986319 |
| 5° | 2923142 |
| 10° | 2664223 |
| 15° | 2081319 |
| 20° | 1232233 |
| 25° | 458083 |
| 30° | 143162 |
| 35° | 63661 |
| 40° | 29561 |
| 45° | 13885 |
| 50° | 7675 |
| 55° | 4301 |
| 60° | 1973 |
| 65° | 1167 |
| 70° | 1442 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P279891

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBAD1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 545.6 | 25.1 |
| 10°-20° | 1085.0 | 50.0 |
| 20°-30° | 444.4 | 20.5 |
| 30°-40° | 73.6 | 3.4 |
| 40°-50° | 17.4 | 0.8 |
| 50°-60° | 4.6 | 0.2 |
| 60°-70° | 1.1 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2075.0 | 95.5 |
| 0°-40° | 2148.5 | 98.9 |
| 0°-60° | 2170.6 | 99.9 |
| 0°-90° | 2171.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2171.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6053 | |
| 5° | 5902 | 546 |
| 15° | 4075 | 1085 |
| 25° | 842 | 444 |
| 35° | 106 | 74 |
| 45° | 20 | 17 |
| 55° | 5 | 5 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P279891

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 6053.0 |
| 1° | 6032.0 |
| 2° | 6004.1 |
| 3° | 5979.2 |
| 4° | 5946.3 |
| 5° | 5902.4 |
| 6° | 5837.6 |
| 7° | 5752.9 |
| 8° | 5632.2 |
| 9° | 5485.6 |
| 10° | 5318.1 |
| 11° | 5123.7 |
| 12° | 4904.4 |
| 13° | 4654.1 |
| 14° | 4376.0 |
| 15° | 4074.9 |
| 17.5° | 3231.4 |
| 20° | 2347.0 |
| 22.5° | 1502.5 |
| 25° | 841.5 |
| 27.5° | 443.7 |
| 30° | 251.3 |
| 32.5° | 159.5 |
| 35° | 105.7 |
| 37.5° | 69.8 |
| 40° | 45.9 |
| 42.5° | 29.9 |
| 45° | 19.9 |
| 47.5° | 14.0 |
| 50° | 10.0 |
| 52.5° | 7.0 |
| 55° | 5.0 |
| 57.5° | 3.0 |
| 60° | 2.0 |
| 62.5° | 1.0 |
| 65° | 1.0 |
| 67.5° | 1.0 |
| 70° | 1.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P279891

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)