

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279802

Luminaire Tested: **LDA2B159040D010 EU2B15FL409040 2LBALD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279802  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159040D010 EU2B15FL409040 2LBALD1LI  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1317.1 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279802

CATALOG NUMBER: LDA2B159040D010 EU2B15FL409040 2LBALD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P279802

CATALOG NUMBER: LDA2B159040D010 EU2B15FL409040 2LBALD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1811082
5°	1772784
10°	1615787
15°	1262255
20°	747320
25°	277789
30°	86820
35°	38606
40°	17904
45°	8442
50°	4605
55°	2580
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279802

CATALOG NUMBER: LDA2B159040D010 EU2B15FL409040 2LBALD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	330.9	25.1
10°-20°	658.0	50.0
20°-30°	269.5	20.5
30°-40°	44.6	3.4
40°-50°	10.5	0.8
50°-60°	2.8	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.4	95.5
0°-40°	1303.0	98.9
0°-60°	1316.3	99.9
0°-90°	1317.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1317.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3671	
5°	3580	331
15°	2471	658
25°	510	269
35°	64	45
45°	12	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279802

CATALOG NUMBER: LDA2B159040D010 EU2B15FL409040 2LBALD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3670.9
1°	3658.2
2°	3641.3
3°	3626.2
4°	3606.2
5°	3579.6
6°	3540.3
7°	3488.9
8°	3415.7
9°	3326.9
10°	3225.3
11°	3107.4
12°	2974.3
13°	2822.6
14°	2653.9
15°	2471.3
17.5°	1959.7
20°	1423.4
22.5°	911.2
25°	510.3
27.5°	269.1
30°	152.4
32.5°	96.7
35°	64.1
37.5°	42.3
40°	27.8
42.5°	18.1
45°	12.1
47.5°	8.5
50°	6.0
52.5°	4.2
55°	3.0
57.5°	1.8
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279802

CATALOG NUMBER: LDA2B159040D010 EU2B15FL409040 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)