

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500212

Luminaire Tested: **LDA2B208030R20D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500212  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208030R20D010 2LBD1MMS  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2005.6 lumens  
Efficiency: N/A  
Efficacy: 97.4 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500212  
CATALOG NUMBER: LDA2B208030R20D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P500212

CATALOG NUMBER: LDA2B208030R20D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	110	113	111	110	109	108	106	105	104	103	102	101	100	99	98
2	112	109	106	104	110	107	105	103	104	102	101	102	100	99	99	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	97	96	97	96	94	93
4	107	102	99	96	105	101	98	95	99	96	94	97	95	93	96	94	92	91
5	104	99	95	93	103	98	95	92	97	94	92	95	93	91	94	92	90	89
6	102	96	93	90	101	96	92	90	94	92	89	93	91	89	92	90	88	87
7	100	94	91	88	99	94	90	88	92	90	87	92	89	87	91	88	87	86
8	98	92	88	86	97	91	88	86	91	88	86	90	87	85	89	87	85	84
9	96	90	87	84	95	90	86	84	89	86	84	88	86	84	88	85	83	83
10	94	88	85	83	93	88	85	82	87	84	82	87	84	82	86	84	82	81

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7433433
5°	6193452
10°	3632252
15°	1272215
20°	428210
25°	165051
30°	75768
35°	33547
40°	16359
45°	9559
50°	5219
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P500212

CATALOG NUMBER: LDA2B208030R20D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1023.2	51.0
10°-20°	768.3	38.3
20°-30°	161.4	8.0
30°-40°	38.7	1.9
40°-50°	11.1	0.6
50°-60°	2.4	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1952.9	97.4
0°-40°	1991.6	99.3
0°-60°	2005.0	100.0
0°-90°	2005.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2005.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15067	
5°	12506	###
15°	2491	768
25°	303	161
35°	56	39
45°	14	11
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500212

CATALOG NUMBER: LDA2B208030R20D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15066.9
1°	14883.1
2°	14433.3
3°	13914.9
4°	13335.0
5°	12505.8
6°	11625.6
7°	10648.7
8°	9532.8
9°	8406.3
10°	7250.4
11°	6061.2
12°	5013.8
13°	3991.9
14°	3177.3
15°	2490.8
16°	1953.9
17°	1541.2
18°	1239.0
19°	1004.3
20°	815.6
22.5°	494.8
25°	303.2
27.5°	198.5
30°	133.0
32.5°	81.2
35°	55.7
37.5°	38.1
40°	25.4
42.5°	18.6
45°	13.7
47.5°	9.8
50°	6.8
52.5°	3.9
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P500212

CATALOG NUMBER: LDA2B208030R20D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)