

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500232

Luminaire Tested: **LDA2B208030R20D010 2LBDL1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1092.0 lumens
Efficiency: N/A
Efficacy: 53.0 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500232

CATALOG NUMBER: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P500232

CATALOG NUMBER: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17366	17366	17366
5°	33182	15353	11193
10°	79254	13426	7565
15°	461834	10675	3014
20°	2303808	6615	893
25°	4200806	2286	0
30°	4927036	0	0
35°	4312410	0	0
40°	3184639	0	0
45°	1147887	0	0
50°	239087	0	0
55°	54706	688	0
60°	17366	789	0
65°	3852	1985	0
70°	0	2452	1154
75°	0	3241	0
80°	0	4830	0
85°	0	9623	0



TEST NUMBER: P500232

CATALOG NUMBER: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.0	0.4
10°-20°	60.0	5.5
20°-30°	404.4	37.0
30°-40°	472.5	43.3
40°-50°	137.8	12.6
50°-60°	9.2	0.8
60°-70°	1.7	0.2
70°-80°	1.4	0.1
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.4	42.9
0°-40°	940.8	86.2
0°-60°	1087.8	99.6
0°-90°	1092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	35	35	35	35	35	
5°	67	49	31	26	23	9
15°	904	102	21	11	6	472
25°	7717	158	4	0	0	3417
35°	7160	85	0	0	0	4399
45°	1645	18	0	0	0	1516
55°	64	3	1	1	0	81
65°	3	2	2	2	0	5
75°	0	2	2	2	0	0
85°	0	2	2	2	0	0
90°	0	0	0	0	0	



TEST NUMBER: P500232

CATALOG NUMBER: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2
2.5°	45.2	45.2	40.2	36.0	32.7	31.0	30.1	28.5	27.6
5°	67.0	58.6	48.6	37.7	31.0	28.5	26.0	23.4	22.6
7.5°	98.0	85.4	58.6	38.5	29.3	25.1	22.6	20.1	18.4
10°	158.2	123.1	72.0	38.5	26.8	21.8	18.4	15.9	15.1
12.5°	292.2	188.4	86.2	37.7	24.3	18.4	14.2	12.6	10.0
15°	904.2	390.2	102.1	36.0	20.9	14.2	10.9	6.7	5.9
17.5°	2338.4	910.9	113.9	31.8	16.7	10.0	5.0	4.2	4.2
20°	4388.0	1651.9	130.6	27.6	12.6	6.7	3.3	2.5	1.7
21°	5005.9	2021.1	139.0	26.0	10.9	4.2	2.5	0.8	0.8
22°	5966.2	2423.8	145.7	24.3	9.2	2.5	1.7	0.8	0.0
23°	6650.2	2680.9	152.4	21.8	6.7	2.5	0.8	0.0	0.0
24°	7334.3	3008.2	156.6	20.1	5.9	1.7	0.8	0.0	0.0
25°	7716.9	3281.2	158.2	18.4	4.2	0.8	0.0	0.0	0.0
26°	8031.7	3463.7	159.1	16.7	2.5	0.0	0.0	0.0	0.0
27°	8301.3	3675.5	157.4	15.1	2.5	0.0	0.0	0.0	0.0
28°	8454.5	3710.7	154.9	13.4	0.8	0.0	0.0	0.0	0.0
29°	8520.6	3668.0	147.4	11.7	0.8	0.0	0.0	0.0	0.0
30°	8648.7	3627.8	139.8	10.9	0.0	0.0	0.0	0.0	0.0
31°	8530.7	3494.7	130.6	9.2	0.0	0.0	0.0	0.0	0.0
32°	8068.5	3382.5	119.7	7.5	0.0	0.0	0.0	0.0	0.0
33°	7930.4	3152.2	108.0	6.7	0.0	0.0	0.0	0.0	0.0
34°	7670.0	2809.8	98.0	5.9	0.0	0.0	0.0	0.0	0.0
35°	7160.1	2526.8	85.4	5.0	0.0	0.0	0.0	0.0	0.0
36°	6804.3	2203.6	74.5	4.2	0.0	0.0	0.0	0.0	0.0
37°	6431.7	1921.5	66.1	3.3	0.0	0.0	0.0	0.0	0.0
38°	5968.7	1625.1	56.1	2.5	0.0	0.0	0.0	0.0	0.0
39°	5429.5	1342.9	47.7	2.5	0.0	0.0	0.0	0.0	0.0
40°	4944.8	1082.6	41.0	1.7	0.0	0.0	0.0	0.0	0.0
42.5°	3051.8	617.9	24.3	1.7	0.0	0.0	0.0	0.0	0.0
45°	1645.2	375.1	17.6	0.8	0.0	0.0	0.0	0.0	0.0
47.5°	757.7	175.0	12.6	0.8	0.0	0.0	0.0	0.0	0.0
50°	311.5	77.9	9.2	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	112.2	43.5	5.9	0.0	0.0	0.8	0.0	0.0	0.0
55°	63.6	25.1	3.3	0.8	0.8	0.8	0.8	0.0	0.0
57.5°	30.1	14.2	0.8	0.8	0.8	0.8	0.8	0.0	0.0
60°	17.6	7.5	0.8	0.8	0.8	1.7	0.8	0.0	0.0
62.5°	8.4	2.5	0.8	1.7	1.7	1.7	1.7	0.8	0.0
65°	3.3	0.8	1.7	1.7	1.7	2.5	1.7	0.8	0.0
67.5°	0.8	0.8	1.7	1.7	1.7	2.5	1.7	0.8	0.8
70°	0.0	0.8	1.7	1.7	1.7	2.5	1.7	0.8	0.8
72.5°	0.0	0.8	1.7	1.7	1.7	2.5	1.7	0.8	0.8
75°	0.0	0.8	1.7	1.7	1.7	1.7	1.7	0.8	0.0
77.5°	0.0	0.8	1.7	1.7	1.7	1.7	1.7	0.8	0.0
80°	0.0	0.8	1.7	1.7	1.7	1.7	1.7	0.8	0.0



TEST NUMBER: P500232

CATALOG NUMBER: LDA2B208030R20D010 2LBDL1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.8	1.7	1.7	1.7	1.7	1.7	0.8	0.0
85°	0.0	0.8	1.7	1.7	1.7	1.7	1.7	0.8	0.0
87.5°	0.0	0.8	1.7	1.7	1.7	1.7	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)