

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500239

Luminaire Tested: **LDA2B208030R20D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R20D010 2LBDLC1MB
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2005.6 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500239

CATALOG NUMBER: LDA2B208030R20D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P500239

CATALOG NUMBER: LDA2B208030R20D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	105	104	103	102	102	100	100	99	99	97	97	97	97
2	112	109	106	104	110	107	105	102	104	102	100	100	101	100	98	98	98	97	96	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	96	99	97	95	95	97	95	94	94	92	92	92	92
4	106	101	98	95	104	100	97	94	98	95	93	93	96	94	92	92	95	93	91	91	90	90	90	90
5	103	98	94	92	102	97	94	91	96	93	90	90	94	92	90	90	93	91	89	89	88	88	88	88
6	101	95	91	89	100	95	91	88	93	90	88	88	92	89	87	87	91	89	87	87	86	86	86	86
7	98	93	89	86	97	92	89	86	91	88	86	86	90	87	85	85	89	87	85	85	84	84	84	84
8	96	90	87	84	95	90	86	84	89	86	84	84	88	85	83	83	87	85	83	83	82	82	82	82
9	94	88	85	82	93	88	84	82	87	84	82	82	86	84	82	82	86	83	81	81	81	81	81	81
10	92	86	83	80	91	86	83	80	85	82	80	80	85	82	80	80	84	82	80	80	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	6630338
5°	5604208
10°	3414680
15°	1404861
20°	505809
25°	202830
30°	92175
35°	43364
40°	22863
45°	12350
50°	7215
55°	3613
60°	2072
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P500239

CATALOG NUMBER: LDA2B208030R20D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	933.4	46.5
10°-20°	807.3	40.3
20°-30°	194.6	9.7
30°-40°	49.9	2.5
40°-50°	15.0	0.7
50°-60°	4.3	0.2
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1935.4	96.5
0°-40°	1985.3	99.0
0°-60°	2004.6	100.0
0°-90°	2005.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2005.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13439	
5°	11316	933
15°	2750	807
25°	373	195
35°	72	50
45°	18	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500239

CATALOG NUMBER: LDA2B208030R20D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	13439.1
1°	13322.2
2°	13043.5
3°	12619.8
4°	12073.8
5°	11316.0
6°	10533.2
7°	9668.9
8°	8771.2
9°	7763.9
10°	6816.1
11°	5825.5
12°	4957.1
13°	4135.6
14°	3382.0
15°	2750.5
16°	2228.6
17°	1799.5
18°	1452.0
19°	1194.1
20°	963.4
22.5°	593.9
25°	372.6
27.5°	242.2
30°	161.8
32.5°	106.5
35°	72.0
37.5°	50.1
40°	35.5
42.5°	25.1
45°	17.7
47.5°	13.6
50°	9.4
52.5°	6.3
55°	4.2
57.5°	3.1
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P500239

CATALOG NUMBER: LDA2B208030R20D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)