

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498837

Luminaire Tested: **LDA2B159030R60D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159030R60D010 2LBD1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1119.0 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498837

CATALOG NUMBER: LDA2B159030R60D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P498837

CATALOG NUMBER: LDA2B159030R60D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	669936
5°	635995
10°	622609
15°	602652
20°	551013
25°	489220
30°	365966
35°	206583
40°	77800
45°	34816
50°	16963
55°	3441
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P498837

CATALOG NUMBER: LDA2B159030R60D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	10.9
10°-20°	327.7	29.3
20°-30°	400.4	35.8
30°-40°	218.4	19.5
40°-50°	43.7	3.9
50°-60°	6.2	0.6
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.7	75.9
0°-40°	1068.1	95.4
0°-60°	1118.0	99.9
0°-90°	1119.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1119.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1358	
5°	1284	122
15°	1180	328
25°	899	400
35°	343	218
45°	50	44
55°	4	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498837

CATALOG NUMBER: LDA2B159030R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1357.9
1°	1351.7
2°	1339.8
3°	1323.9
4°	1301.2
5°	1284.2
6°	1275.2
7°	1264.4
8°	1255.9
9°	1251.9
10°	1242.8
11°	1232.6
12°	1223.6
13°	1212.8
14°	1196.9
15°	1179.9
16°	1158.4
17°	1128.3
18°	1109.0
19°	1077.8
20°	1049.5
21°	1023.4
22.5°	979.8
23°	961.6
24°	933.8
25°	898.7
26°	853.9
27°	806.8
28°	753.0
29°	701.9
30°	642.4
32.5°	492.7
35°	343.0
37.5°	214.9
40°	120.8
42.5°	75.4
45°	49.9
47.5°	34.0
50°	22.1
52.5°	11.3
55°	4.0
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6



TEST NUMBER: P498837

CATALOG NUMBER: LDA2B159030R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)